


P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-15-005230	10APR2015	KG	DW
	B1	ECR-17-016330	08NOV2017	KG	DW

1. SHIPPED ASSEMBLED AS SHOWN.
2. ALL ASSEMBLY DIMENSIONS ARE FOR REFERENCE ONLY.
3. INSERTION LOSS: -1: 4 dB MAXIMUM
-2: 1.6 dB MAXIMUM
-3: 1.8 dB MAXIMUM
-4: 1.8 dB MAXIMUM
-5: 1.6 dB MAXIMUM

- 4

 RETURN LOSS: 34 dB MINIMUM.
- 5

 A1-B1 LOOP, ONLY.



FIBER PATH	
LOOP 1	LOOP 2
A1-B1	A2-B2



1516506-X
XXXXXXXXXX

TE LOGO

TE PART NUMBER


TE SERIAL NUMBER

LABEL DETAIL
(NOT TO SCALE)

5	1	OM3 50/125 MM	1516506-5
4	2	1550 SM	1516506-4
4	2	1310 SM	1516506-3
	2	OM3 50/125 MM	1516506-2
	2	62.5/125 MM	1516506-1
NUMBER OF LOOPS		DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL
-
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH
HARD ANODIZE
-

DWN
K. GLATFELTER
09OCT2012

CHK
D. WERTMAN
09OCT2012

APVD
D. WERTMAN
09OCT2012

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
LOOPBACK PLUG, ASSEMBLY,
PRO BEAM JR.

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-1516506

RESTRICTED TO
-

SCALE
2:1

SHEET
1

OF
1

REV
B1