



REVISION					
ZONE	LTR	ECN	DESCRIPTION	DATE	APPROVED
	B	39399	GENERAL DWG UPDATE	8/22/99	SLC



1532143-8

NOTES: UNLESS OTHERWISE SPECIFIED

1. MARK PER TIS.
2. POTTING COMPOUND USED IS 194-8102-6215/6225.
3. CRIMP LEADS INTO CONTACTS PER MEP 302-05.
4. EPOXY WICKING FROM THE REAR OF THE CONNECTOR ON INSULATED LEADS MUST NOT EXCEED .125 MAX ON #25 AWG AND SMALLER LEADS AND .200 MAX ON #24 AWG AND LARGER LEADS.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCE ARE:		APPROVALS		 MICRODOT CONNECTORS A DIVISION OF UNI-STAR INDUSTRIES INC. 325 PASADENA AVE., SO. PASADENA, CA 91030	
FRACTIONS ± 1/8	DECIMALS .XX ± .01 .XXX ± .005	ANGLES ± 2°			
MATERIAL:		SIGNATURE	DATE	METAL SHELL 'D' CONNECTOR MCDMI-B-11'S	
		DRAWN BY MEL F. CAMPBELL	09/20/99		
		P.E. J. L. GUNGE	8/22/99		
		M.E.			
FINISH:		THIS DOCUMENT IS THE PROPERTY OF MICRODOT CONNECTORS, A DIVISION OF UNI-STAR INDUSTRIES INC. USE OF THIS DOCUMENT OR ANY PART THEREOF IS STRICTLY FORBIDDEN WITHOUT THE EXPRESS WRITTEN PERMISSION OF MICRODOT CONNECTORS, A DIVISION OF UNI-STAR INDUSTRIES INC.		PROD CODE 842	CODE M
		SIZE A	CODE IDENT NO. 98278	DRAWING NO. 095-0000-0092	
		SCALE: NONE		SHEET 1 OF 1	