




CONNECTOR ASSEMBLY
EXEMPLARY LOADED



CONTACT DIMENSIONS


SCALE 5:1



CONTACT LAYOUT

	z	a	b	c	d	e	f
1	C	A	A	A	A	A	C
2	C	A	A	A	A	A	C
3	C	A	A	A	A	A	C
4	C	A	A	A	A	A	C
5	C	A	A	A	A	A	C
6	C	A	A	A	A	A	C
7	C	A	A	A	A	A	C
8	C	A	A	A	A	A	C
9		A	A	A	A	A	
10		A	A	A	A	A	
11		A	A	A	A	A	
12	C	A	A	A	A	A	C
13	C	A	A	A	A	A	C
14	C	A	A	A	A	A	C
15	C	A	A	A	A	A	C
16	C	A	A	A	A	A	C
17	C	A	A	A	A	A	C
18	C	A	A	A	A	A	C
19	C	A	A	A	A	A	C


RECOMMENDED PCB-HOLE LAYOUT
COMPONENT SIDE SHOWN



PLATED THRU HOLES PARAMETERS

REFERENCE APPLICATION SPECIFICATION

	1645590-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN 11/18/2010 RAYMOND CAO		Tyco Electronics Corporation Shanghai P.R.China 200233	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0-FILE ± 1-FILE ±0.1 2-FILE ±0.1 3-FILE ± 4-FILE ± ANGLES ±		NAME MALE ASSEMBLY, Z-PACK 2mm HM, TYPE A/B	
		PRODUCT SPEC 108-19082		SIZE CAGE CODE DRAWING NO. RESTRICTED TO	
MATERIAL 		APPLICATION SPEC 114-19029		A1 00779 C-1645590	
FINISH SEE TABLE		WEIGHT —		SCALE 4:1 SHEET 1 OF 2 REV. A	
		CUSTOMER DRAWING			

LOC		DIST		REVISIONS					
AD		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
					—	SEE SHEET 1	—	—	—

- 1

MATERIAL:
CONTACT: PHOSPHOR BRONZE.
HOUSING: GLASS-FILLED POLYESTER.
- 2

GENERAL PLATING SPECIFICATION: UNDERPLATING
(ENTIRE CONTACT): 1.27μm MIN NICKEL AND ACTION
PIN: 0.5μm MIN TIN/LEAD.
1.26μm MIN. GOLD PLATING AT MATING SURFACES.
- 3

CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101
PERFORMANCE LEVEL 1.
- 4


CONNECTOR MARKED WITH PART NUMBER AND DATE CODE.
ADDITIONAL CHARACTERS OR MARKINGS, AS WELL AS THE LOCATION OF THE MARKINGS,
MAY BE ADDED FOR TRACEABILITY BASED UPON MANUFACTURERS DISCRETION.
- 5

PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
PATTERN DEFINED BY CONTACT LAYOUT.
- 6

FOR ACTUAL PIN LOADING SEE "CONTACT LAYOUT".
- 7

FOR ACTUAL PIN DIMENSIONS SEE "CONTACT DIMENSIONS".
- 8

TO BE MEASURED AT BOTTOM OF SHROUD.

THIS DRAWING IS A CONTROLLED DOCUMENT.				DRN B CARBO	07SEP05	 Tyco Electronics Corporation Shanghai P.R.China 200233			
				CHK G.SKIPPER	07SEP05				
				APVD G.SKIPPER	07SEP05				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	MALE ASSEMBLY, Z-PACK 2mm HM, TYPE A/B				
		0-PLC ± —		PRODUCT SPEC	108-19082				
		1-PLC ± 0.1							
		2-PLC ± —		APPLICATION SPEC	114-19029				
		3-PLC ± —							
MATERIAL SEE SHEET 1		4-PLC ± —		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
		FINISH SEE SHEET 1		WEIGHT	A1 00779		©=1645590	—	
CUSTOMER DRAWING				SCALE	4:1	SHEET	2 OF 2	REV	A