

DO NOT SCALE

DIMENSIONS IN mm

METRIC


THIRD ANGLE
PROJECTION



NOTES:

- ① DUPLEX PL.:
 - UNDERLAYER 1,25 µM MIN. NICKEL PER 112-25-2
 - ZONE I : OVER 3,8 MIN. LENGTH OUTSIDE+EDGES 0,75 µM MIN. GOLD PER 166938-1.
 - ZONE II : OVER 8,6 MIN. LENGTH OUTSIDE 0,75 µM MIN. PER 112-26-1
 - ZONE III: OVER 15,7 MIN. 2,5 µM ±1,3 TIN/LEAD 93/7 PER 112-26-1

- ② LUBRICATED
- ③ REVERSE REELED FOR MINI APPLICATOR
- ④ TERMINAL LATCH NYLON
- ⑤ LOOSE PIECE



| | | | | |
|------------|----------|---------|----------|--------------|
| 12 -16 AWG | 4,06 MAX | ① | COPPER | ⑤ 164773-5 |
| 12 -16 AWG | 4,06 MAX | ① | COPPER | ③ 1-164773-4 |
| 12 -16 AWG | 4,06 MAX | ① | COPPER | 164773-4 |
| WIRE SIZE | INS SIZE | PLATING | MATERIAL | PARTNUMBER |

| | | | | | |
|--|------------------------------|-----|------|----------|---|
| CUSTOMER DRAWING | | | | | FOR REFERENCE ONLY WILL NOT BE UPDATED |
| © COPYRIGHT 19- BY AMP-HOLLAND B.V. | | | | | |
| ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING. | | | | | |
| THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION | | | | | |
| Y | ECN H-9431 | MvD | RD | 08-01-92 | AMP-HOLLAND B.V. 's-Hertogenbosch, The Netherlands. |
| W | ECN H-9184 | MvD | RD | 07-10-91 | |
| V | ECN H-8989 | MvD | RD | 01-08-91 | |
| U | REVISED & REDRAWN ECN H-8854 | MvD | RD | 03-05-91 | |
| LTR. | REVISION RECORD | DR. | CHK. | DATE | NAME |
| FEMALE TYPE XII CONT. ASS'Y. | | | | | - |

| | | | | | |
|--------|--------|--------------|----------|-----------|--------|
| DR. - | CHK. - | APP. | DWG. No. | REV. LTR. | SHEET |
| DATE - | DATE - | DATE 15-1.92 | C-164773 | Y | 1 OF 1 |