

D

C

B




A

D

C

B

A







NOTES:

- 1 PLATING: 0,5µm MIN. TIN OVER NICKEL.
- 2 PLATING:

PARTNUMBER	PERFORMANCE LEVEL
1551014-1	PERFORMANCE LEVEL 1: CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III: UNCONTROLLED ENVIRONMENT APPLICATIONS. SEE PRODUCT SPEC 108-19353
1551014-2	PERFORMANCE LEVEL 2: CONFORMS TO ALL TESTING ACCORDING PRODUCT SPEC 108-19320, -250 MATING CYCLES, 4 DAYS MIXED GAS TEST PER IEC 60068-2-60 METHOD 1

- 3 CONSULT APPLICATION SPEC OR CONTACT TE CONNECTIVITY FOR PERMISSIBLE CONTACT ASSIGNMENTS.
- 4 BLACK SQUARE MARKING FOR LEVEL 1 PIN AT POSITION a12 AS INDICATED.
- 5 CONNECTOR MARKED WITH PARTNUMBER AND DATE CODE.
- 6 FOR PC-BOARD ROUTING RECOMMENDATIONS SEE SPEC 114-19140



PRODUCT HAS NOT COMPLETED
QUALIFICATION TESTING

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	Vathsa	02 Dec 08
DIMENSIONS:		CHK	R. Annokke	02 Dec 08
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	Mark Westen	02 Dec 08
mm		PRODUCT SPEC	SEE NOTE 4	
MATERIAL		APPLICATION SPEC	114-19106	
-		WEIGHT	-	
-		CUSTOMER DRAWING	-	
3 OVERMOLD		LCP 30% GF NATURAL		
2 HOUSING		LCP 30% GF NATURAL		
1 CONTACT		COPPER ALLOY		
ITEM NO.		DESCRIPTION		MATERIAL
NAME		MALE CONNECTOR		
SIZE		CAGE CODE		RESTRICTED TO
A2		00779		-
DRAWING NO		1551014		
SCALE		5:1		
SHEET		1 OF 1		
REV		A		