


4805 (3/13)

| 5 4 | 3 | |
|-----|---|--|



| | | REVISIONS | | | |
|---|-----|-----------------------------------|-----------|-----|------|
| P | LTR | DESCRIPTION | DATE | DWN | APVD |
| | D | REDRAWN/REVISED PER ECO-17-001755 | 21NOV2017 | KS | JO |
| | | | | | |
| | | | | | |
| | | | | | |

1

1 HOUSING:FLAME RETARDANT THERMOPLASTIC, COLOR-BLACK

2 CONTACT:COPPER ALLOY

4. NOTE DELETED.

7. NOTE DELETED.

10. NOTE DELETED.

13.NOTE DELETED.

14.NOTE DELETED.


CONTACT AREAS PLATED WITH 0.76µM MIN GOLD;SOLDER TAILS PLATED WITH 3.81µM MIN TIN-LEAD,ALL OVER 1.27µM MIN NICKEL

5 DIMENSION APPLIES AT BASE OF SHROUD 6 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING

A DIMENSION FOR DIAMETER OF PEG APPLIES AT THE INTERSECTION OF THE TOP OF RIBS AND BASE OF PAG.

CONTACT AREAS PLATED WITH 0.76µM MIN GOLD; SOLDER TAILS PLATED WITH 3.81µM MIN TIN,ALL OVER 1.27µM MIN NICKEL.

INTERPOSED FINISH: 0.03μM MIN GOLD ON GOLD PLATED AREA, 3.81μM MATTE TIN LEAD ON TIN PLATE AREA. UNDER PLATING SHOULD BE 1.27μM NICKEL ON ENTIRE CONTACT, GOLD AND TIN PLATING MAY NOT OVERLAP. FINISH: 0.03µM MIN GOLD ON GOLD PLATED AREA, 3.81µM MATTE TIN ON TIN PLATE AREA.UNDER PLATING SHOULD BE 1.27µM NICKEL ON ENTIRE CONTACT, GOLD AND TIN PLATING MAY NOT OVERLAP.



| | | 12 | 22.35 | | 14 | 30 | 5-1571697-1 |
|--|-------|-------------|--------|-------------|-------------|-------------------------|------------------------|
| | | <u>_9</u> | 22.35 | | 14 | 30 | 5-1571697-1 |
| | | | 22.35 | | 14 | 30 | 2-1571697-1 |
| | | 3 | 22.35 | | 14 | 30 | 1571697-1 |
| | F | INISH | DIM_B |) | A SPACES | NO OF POSN | P A R T N U M B E R |
| CONTROLLED DOCUMENT. CONTROLLED DOCUMENT. CHK J. OLSON DWN 21NOV2017 J. OLSON | | | | | - 21 | TE Co | nnectivity |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 21NOV2017 1 PLC ±- 2 PLC ±0.3 3 PLC ±0.13 | | | | | | | |
| 4 PLC ±- ANGLES FINISH SEE NC | ±0.5° | - WEIGHT | | size A 1 | | ^{NO} 571697 | RESTRICTED TO - |
| CUSTOMER DRAWING | | | RAWING | | | SCALE 6:1 SHEE | et of rev D |