

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION
— ,N/A .

© COPYRIGHT N/A BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
—	—	P	LTR	DESCRIPTION	DATE	APVD
			D	REV PER ECO 09-020247	9-4-09	CT WM

COMPONENT	MATERIAL AND FINISH
BODY & PIN	KOVAR MIL-I-23011 GOLD PLATE PER MIL-G-45204 AND ASTM-F15 TYPE 1, GRADE C, CLASS 1
GLASS	CORNING #7070 OR EQUIVALENT



- 1

SOLDER DIPPED OVER LENGTH OF PIN. SOLDER ALLOWED TO HEIGHT OF .060 MAX ON HOUSING. MUST MEET SOLDERABILITY REQUIREMENTS OF METHOD 208, MIL-STD-202.
2. PARTS PACKAGED IN TAPE ON 13 INCH DIAMETER REELS PER EIA 481.

1	1663433-4
	1663433-1
REMARKS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 21APR2003	Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105			
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK R.GROSS 4-22-03				
	0 PLC ± - 1 PLC ± - 2 PLC ± .01 3 PLC ± .005 4 PLC ± - ANGLES ± -	APVD R.GROSS 4-22-03	NAME SMPM,HERMETIC SMOOTH BORE SHROUD, 50 OHM IMPEDANCE			
		PRODUCT SPEC				
		APPLICATION SPEC				
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C-1663433	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 20:1	SHEET 1	OF 1	REV D