


NOTES Bemerkungen			MARKING FOR PINOUT-CONFIGURATION Markierung fuer Pinout-Konfiguration 6 TE PN TE Nr.			PINOUT CONFIGURATION																															
						BLANKED CAVITIES INDICATE CLOSED LOCATIONS Leere Felder kennzeichnen geschlossene Kammern																															
						WITH "X" MARKED CAVITIES INDICATE OPEN LOCATIONS Markierte Felder mit "X" kennzeichnen offene Kammern																															
						1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32
SPA2	133	3-2177515-3	0	X	X	X					X	X	X	X	X			X	X	X	X		X		X	X	X			X		X					
SPA2	132	3-2177515-2	0	X	X	X					X	X	X	X	X			X	X	X	X		X	X		X	X	X			X	X	X				
SPA2	131	3-2177515-1	0	X	X	X					X	X	X	X	X			X	X	X	X			X	X	X	X				X	X	X				
CMA	130	3-2177515-0	0					X	X		X				X	X		X	X			X			X	X	X	X		X		X	X				
SPA	129	2-2177515-9	0					X	X		X				X	X		X	X			X			X	X	X	X			X	X	X				
SPA2	128	2-2177515-8	0	X	X	X				X	X	X	X	X			X	X	X	X			X			X	X	X				X					
FORD FOCUS SA	127	2-2177515-7	0					X						X	X	X	X	X	X	X	X			X	X	X	X	X	X								
SPA	126	2-2177515-6	0					X	X		X			X	X	X	X	X	X			X			X	X	X	X	X		X	X	X				
FORD FOCUS SA	125	2-2177515-5	0				X		X					X	X		X	X	X	X	X			X	X	X	X	X	X				X	X			
B562APA, B562MCA	124	2-2177515-4	0	X	X					X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X			
SPA	123	2-2177515-3	0			X		X	X	X	X			X	X	X	X	X	X			X			X	X	X	X	X		X	X	X	X			
C490	122	2-2177515-2	0						X						X	X	X	X	X	X	X	X			X	X	X	X	X		X	X	X	X			
B515	121	2-2177515-1	0			X			X					X		X	X	X	X	X	X	X			X	X	X	X	X	X	X	X	X	X			
-	119	1-2177515-9	0	X	X				X		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X			
-	118	1-2177515-8	0	X	X			X		X	X	X	X	X			X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X			
B299 MCA	117	1-2177515-7	0		X			X	X	X	X	X	X	X			X	X			X			X		X	X	X									
B299MCA	116	1-2177515-6	0					X					X		X	X	X	X	X	X	X	X			X	X	X	X	X	X	X	X	X	X			
B299MCA	115	1-2177515-5	0					X					X		X	X	X	X			X			X	X				X	X	X	X	X	X			
B299MCA	114	1-2177515-4	0				X		X					X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X			
B299MCA	113	1-2177515-3	0					X						X	X	X	X	X	X	X	X	X	X			X	X			X	X	X	X	X			
B299MCA	112	1-2177515-2	0				X		X					X	X	X	X	X	X	X	X	X	X			X	X	X	X	X	X	X	X	X			
B299MCA	111	1-2177515-1	0					X						X	X	X	X	X	X	X	X	X	X			X	X	X	X	X	X	X	X	X			
B299MCA	110	1-2177515-0	0					X						X		X	X	X	X			X			X	X	X			X	X	X	X	X			
B299MCA	109	0-2177515-9	0					X					X		X	X	X	X	X	X	X	X			X	X	X	X	X	X	X	X	X	X			
B515	108	0-2177515-8	0			X	X	X					X		X	X	X	X	X	X	X	X			X	X	X	X	X	X	X	X	X	X			
C344N HEV / C344	106	0-2177515-6	0			X	X	X	X	X			X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X			
2L GTDI HEV CD391	105	0-2177515-5	0				X		X	X	X		X	X	X			X	X			X	X	X	X	X	X	X	X	X	X	X	X	X			
-	104	0-2177515-4	0	X			X		X	X	X	X	X	X			X	X			X	X	X	X	X	X	X	X	X	X	X	X	X	X			
B515 / B299 MCA	103	0-2177515-3	0					X					X		X	X	X	X	X	X	X	X	X			X	X	X	X	X	X	X	X	X			
-	099	9-1719675-9	0	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X			
B299MCA / B232 / FORD FOCUS SA	096	9-1719675-6	0					X					X		X	X	X	X	X	X	X	X			X	X	X	X	X	X	X	X	X	X			
Transit	094	9-1719675-4	0	X	X	X	X	X	X	X	X	X		X		X	X	X	X	X	X			X	X	X	X	X	X	X	X	X	X	X			
Transit	093	9-1719675-3	0		X	X	X			X	X	X	X		X		X	X	X	X	X			X	X	X	X	X	X	X	X	X	X	X			
Transit	092	9-1719675-2	0		X	X			X	X	X	X					X	X	X	X	X			X	X	X	X	X						X			
Transit	091	9-1719675-1	0	X	X	X	X			X	X	X	X		X		X	X	X	X	X			X	X	X	X	X	X	X	X	X	X	X			
Transit	090	9-1719675-0	0	X	X	X			X	X	X	X					X	X	X	X	X			X	X	X	X	X	X			X	X	X			
Transit	089	8-1719675-9	0		X	X				X	X	X	X				X	X	X	X	X			X	X	X	X	X	X				X	X			
Transit	088	8-1719675-8	0		X		X	X		X	X	X	X	X	X		X		X	X	X	X			X				X	X		X		X			
Transit	087	8-1719675-7	0		X		X	X	X	X	X	X	X	X	X	X		X	X			X	X					X	X	X	X	X	X	X			
Transit	086	8-1719675-6	0		X			X	X	X	X	X	X	X	X	X		X	X	X	X	X			X	X	X	X	X	X	X	X	X	X			
Transit	085	8-1719675-5	0	X	X		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X			
Transit	084	8-1719675-4	0	X	X		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X			
Transit	083	8-1719675-3	0		X		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X			
Transit	082	8-1719675-2	0		X		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X			
Transit	081	8-1719675-1	0	X				X	X	X	X	X				X					X			X	X	X	X			X	X	X	X	X			
B299 / i06	080	8-1719675-0	0				X		X				X		X	X	X	X	X	X	X	X			X	X	X	X	X	X	X	X	X	X			
B299	079	7-1719675-9	0			X				X	X	X	X		X				X	X	X				X				X				X	X			
-	076	7-1719675-6	0	X	X	X	X			X	X	X	X		X			X	X	X	X			X	X	X	X	X	X	X	X	X	X	X			
-	075	7-1719675-5	0	X	X	X				X	X	X	X					X	X	X	X			X	X	X	X	X	X	X	X	X	X	X			
-	074	7-1719675-4	0		X			X	X	X	X	X	X	X	X	X					X			X	X	X	X	X			X	X	X	X			
-	073	7-1719675-3	0		X	X		X	X	X	X	X	X	X	X	X	X				X			X	X	X	X	X			X	X	X	X			
-	072	7-1719675-2	0	X	X	X	X			X	X	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X	X	X	X	X	X	X			
-	071	7-1719675-1	0		X		X	X		X	X	X	X	X	X			X			X	X			X				X	X		X		X			
-	070	7-1719675-0	0		X	X	X			X	X	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X	X	X	X	X	X	X			
-	069	6-1719675-9	0	X	X	X	X			X	X	X	X	X	X	X	X	X	X	X	X			X	X	X	X	X	X	X	X	X	X	X			
-	068	6-1719675-8	0	X	X	X			X	X	X	X	X					X	X	X	X			X	X	X	X	X									

PINOUT CONFIGURATION																																			
NOTES Bemerkungen	 MARKINGS FOR PINOUT- CONFIGURATION Markierung fuer Pinout- Konfiguration	 TE PN TE Nr.	REV	BLANK CAVITIES INDICATE CLOSED LOCATIONS Leere Felder kennzeichnen geschlossene Kammern																															
				WITH "X" MARKED CAVITIES INDICATE OPEN LOCATIONS Markierte Felder mit "X" kennzeichnen offene Kammern																															
				1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32
-	013	1-1719675-3	0			X	X			X		X	X	X	X			X		X	X	X	X					X	X	X			X	X	
-	012	1-1719675-2	0							X	X	X	X							X	X	X	X		X		X	X	X	X			X	X	
Y285-14-MANAUTO-0820	010	1-1719675-0	0		X		X	X		X	X	X	X		X	X		X		X	X	X	X			X		X	X	X	X			X	
Y285-DW10-MANAUTO-0746	009	0-1719675-9	0	X	X	X				X		X	X	X	X		X	X		X	X	X	X			X	X	X	X		X	X	X		
DV6	004	0-1719675-4	0							X	X	X	X							X	X	X		X		X		X					X	X	
N14 MAN 0720 F32	003	0-1719675-3	0		X		X	X		X	X	X	X	X	X			X		X	X	X	X			X				X	X			X	
DW10 Auto 0746	002	0-1719675-2	0	X		X	X			X		X	X	X	X		X	X		X	X	X	X			X	X	X	X			X	X		
DW10 MAN	001	0-1719675-1	0	X			X						X	X	X			X	X	X	X		X			X			X	X			X	X	

CODING 1

CODING 1
COLOR BLACK
LEVER RIGHT
CABLE EXIT LEFT
PN 1719675 / 2177515

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-		-	SEE SHEET 1	-	-	-

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	16JUL2007	TE Connectivity									
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED :						CHK	19JUL2007				
		0 PLC ± 0.1 1 PLC ± 0.1 2 PLC ± 0.1 3 PLC ± 0.1 4 PLC ± 0.1 ANGLES ± 1°						G. PUCKEL	23JUL2007				
		APVD G. MUMPER PRODUCT SPEC - APPLICATION SPEC 114-18761-1		NAME DIFFERENT PIN OUT CONFIGURATION FOR 32 POS. MIXED RECEPTACLE HOUSING									
								WEIGHT	-				
								MATERIAL	FINISH	-			
-		-		CUSTOMER DRAWING		SCALE	1:1	SHEET	2	OF	6	REV	027

PINOUT CONFIGURATION																																				
NOTES Bemerkungen	7 MARKINGS FOR PINOUT- CONFIGURATION Markierung Für Pinout- Konfiguration	6 TE PN TE Nr.	REV	BLANKED CAVITIES INDICATE CLOSED LOCATIONS Leere Felder kennzeichnen geschlossene Kammern																																
				WITH "X" MARKED CAVITIES INDICATE OPEN LOCATIONS Markierte Felder mit "X" kennzeichnen offene Kammern																																
				1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	
SPA	135	3-2141581-5						X	X		X				X	X			X	X			X				X	X	X	X	X		X	X	X	
SPA2	134	3-2141581-4	□					X	X		X			X	X	X			X	X			X			X	X	X	X	X	X		X	X	X	
SPA	120	2-2141581-0	□			X		X	X	X			X	X	X	X			X	X			X			X	X	X	X	X		X	X	X		
-	107	0-2141581-7	□			X		X	X	X			X	X	X			X	X			X	X	X		X	X		X	X	X		X			
CD34	101	0-2141581-1	□	X	X	X		X	X	X	X	X	X		X			X	X	X					X		X	X							X	X
-	099	9-1670065-9	□	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	

CODING 1

CODING 1
COLOR BLACK
LEVER LEFT
CABLE EXIT RIGHT
PN 1670065 / 2141581

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-		-	SEE SHEET 1	-	-	-


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	16JUL2007	 TE Connectivity DIFFERENT PIN OUT CONFIGURATION FOR 32 POS. MIXED RECEPTACLE HOUSING			
DIMENSIONS: mm		CHK	19JUL2007				
		G. PUCKEL	23JUL2007				
		APVD					
		G. MUMPER					
		PRODUCT SPEC					
		-					
TOLERANCES UNLESS OTHERWISE SPECIFIED :		APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
0 PLC ± 0.1		114-18761-1		A1	00779	 1670065	-
1 PLC ± 0.1		WEIGHT	-				
2 PLC ± 0.1		CUSTOMER DRAWING					
3 PLC ± 0.1							
4 PLC ± 0.1							
ANGLES ± 1°		SCALE 11 SHEET 3 OF 6 REV 027					
MATERIAL							
-							
-							
FINISH							
-							
-							

PINOUT CONFIGURATION																																			
NOTES Bemerkungen	 MARKINGS FOR PINOUT-CONFIGURATION Markierung fuer Pinout-Konfiguration	 TE PN TE Nr.	REV	BLANKED CAVITIES INDICATE CLOSED LOCATIONS Leere Felder kennzeichnen geschlossene Kammern																															
				WITH "X" MARKED CAVITIES INDICATE OPEN LOCATIONS Markierte Felder mit "X" kennzeichnen offene Kammern																															
				1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32
CD34x	102	0-2141582-2	□		X	X				X	X		X	X				X	X		X	X		X	X					X	X	X	X	X	
-	099	9-1719682-9	□	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
Transit	095	9-1719682-5	□	X	X	X			X	X	X	X	X					X	X	X	X	X			X	X	X	X	X	X			X	X	
Transit	094	9-1719682-4	□	X	X	X	X		X	X	X	X	X			X		X	X	X	X	X			X	X	X	X	X	X	X	X		X	X
Transit	093	9-1719682-3	□		X	X	X			X	X	X	X			X		X	X	X	X	X			X	X	X	X	X	X	X	X		X	X
Transit	092	9-1719682-2	□		X	X			X	X	X	X	X					X	X	X	X	X			X	X	X	X	X			X	X	X	
Transit	091	9-1719682-1	□	X	X	X	X			X	X	X	X			X		X	X	X	X	X			X	X	X	X	X	X	X	X		X	X
Transit	090	9-1719682-0	□	X	X	X				X	X	X	X					X	X	X	X	X			X	X	X	X	X			X	X	X	
Transit	089	8-1719682-9	□		X	X				X	X	X	X					X	X	X	X	X			X	X	X	X	X			X	X	X	
Transit	088	8-1719682-8	□		X		X	X		X	X	X	X	X	X			X		X	X	X	X			X				X	X			X	
-	063	6-1719682-3	□	X				X	X	X	X					X			X		X		X	X	X					X	X			X	
-	062	6-1719682-2	□		X			X	X		X		X	X	X	X			X	X		X	X	X				X	X	X	X		X		
-	061	6-1719682-1	□		X		X	X	X	X	X	X	X	X	X	X	X			X	X		X	X	X			X	X	X	X		X	X	
-	060	6-1719682-0	□	X	X		X	X	X	X	X	X	X	X	X	X			X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	059	5-1719682-9	□		X		X	X	X	X	X	X	X	X	X	X			X	X		X	X				X	X	X	X					
-	058	5-1719682-8	□		X		X	X	X		X	X	X	X	X	X			X	X	X	X	X	X			X	X	X	X			X		
-	057	5-1719682-7	□	X	X		X	X	X	X	X	X	X	X	X	X			X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	
-	056	5-1719682-6	□		X		X	X	X	X	X	X	X	X	X	X			X	X	X		X	X			X	X	X	X			X		
-	024	2-1719682-4	□													X	X	X	X				X	X		X					X	X	X	X	
-	023	2-1719682-3	□													X	X	X	X				X			X						X	X	X	

CODING 2

CODING 2
COLOR GREY
LEVER RIGHT
CABLE EXIT LEFT
PN 1719682 / 2141582

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-		-	SEE SHEET 1	-	-	-


THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	16JUL2007	 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED :		CHK	19JUL2007		
				G. PUCKEL			
		0 PLC ± 0.1 1 PLC ± 0.1 2 PLC ± 0.1 3 PLC ± 0.1 4 PLC ± 0.1 ANGLES ± 1°		APVD	23JUL2007		
				G. MUMPER			
				PRODUCT SPEC			
MATERIAL		FINISH		APPLICATION SPEC	114-18761-1	NAME	
				WEIGHT	-		
-		-		CUSTOMER DRAWING		SIZE	RESTRICTED TO
				A1	00779	DRAWING NO	
				1670065		CAGE CODE	
						114-18761-1	
						SCALE	REV
						1:1	027
						SHEET	
						4	
						OF	
						6	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-		-	SEE SHEET 1	-	-	-

CODING 2

CODING 2
COLOR GREY
LEVER LEFT
CABLE EXIT RIGHT
PN 1670066

PINOUT CONFIGURATION																																					
NOTES Bemerkungen	 MARKINGS FOR PINOUT- CONFIGURATION Markierung für Pinout- Konfiguration	 TE PN TE Nr.	REV	BLANKED CAVITIES INDICATE CLOSED LOCATIONS Leere Felder kennzeichnen geschlossene Kammern																																	
				WITH "X" MARKED CAVITIES INDICATE OPEN LOCATIONS Markierte Felder mit "X" kennzeichnen offene Kammern																																	
				1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32		
-	099	9-1670066-9	0	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X		
Transit	086	8-1670066-6	0	X				X	X		X		X	X	X	X	X		X	X		X	X	X			X	X	X	X		X		X			
Transit	085	8-1670066-5	0	X	X			X	X	X	X	X		X	X	X	X	X		X	X	X	X	X	X			X	X	X	X	X	X	X	X		
Transit	084	8-1670066-4	0	X	X			X	X	X	X	X		X	X	X	X	X			X	X	X	X	X	X			X	X	X	X	X	X	X		
Transit	083	8-1670066-3	0		X			X	X	X	X	X		X	X	X	X	X			X	X	X	X				X	X	X	X		X		X		
Transit	082	8-1670066-2	0		X			X	X	X		X		X	X	X	X	X			X	X	X	X				X	X	X	X		X		X		
Transit	081	8-1670066-1	0	X				X	X	X	X				X					X				X	X		X			X	X			X			
-	078	7-1670066-8	0	X	X			X	X	X	X	X		X	X	X	X	X		X	X	X	X	X	X			X	X	X	X	X	X	X	X		
-	077	7-1670066-7	0	X	X			X	X	X	X	X	X		X	X	X	X	X		X	X	X	X	X			X	X	X	X	X	X	X	X		
P1X, DV6B, SOP 0920	054	5-1670066-4	0	X	X			X	X	X	X	X	X		X	X		X	X		X		X	X	X	X	X			X			X	X	X		
-	053	5-1670066-3	0									X	X				X	X		X	X			X				X	X				X	X	X		
-	052	5-1670066-2	0									X	X				X	X		X	X			X	X			X	X				X	X	X		
-	034	3-1670066-4	0	X				X	X	X	X						X	X	X	X		X			X	X	X			X				X	X		
-	033	3-1670066-3	0	X				X	X	X	X			X	X			X	X	X	X		X			X	X	X			X				X	X	
-	032	3-1670066-2	0						X	X							X	X	X		X			X	X					X	X	X	X	X	X		
-	031	3-1670066-1	0		X	X				X	X	X	X				X	X		X	X			X	X					X	X	X	X	X	X		
-	030	3-1670066-0	0	X	X	X		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X		
-	029	2-1670066-9	0	X	X	X		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X		
-	028	2-1670066-8	0	X	X	X		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X		
-	027	2-1670066-7	0	X	X	X		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X		
-	026	2-1670066-6	0	X		X		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X		
-	025	2-1670066-5	0	X		X		X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X		
-	024	2-1670066-4	0	X	X			X	X	X	X	X	X			X	X	X	X		X			X	X	X			X			X			X		
-	023	2-1670066-3	0	X	X			X	X	X	X	X	X				X	X	X		X			X	X	X			X			X			X		
-	022	2-1670066-2	0									X	X					X	X		X	X			X				X	X			X	X	X		
-	020	2-1670066-0	0	X	X	X	X	X	X	X	X	X	X	X	X	X								X	X	X		X	X	X	X	X	X	X	X		
-	019	1-1670066-9	0	X	X	X	X	X	X	X	X	X	X	X	X	X				X				X		X	X	X	X	X	X	X	X	X	X		
-	018	1-1670066-8	0		X	X	X	X	X	X	X	X	X	X	X	X								X		X	X	X	X	X	X	X	X	X	X		
-	017	1-1670066-7	0	X	X			X	X	X	X						X	X	X		X			X			X	X			X			X	X		
-	016	1-1670066-6	0	X	X			X	X	X	X						X	X	X		X			X			X	X			X			X	X		
Y285-14-MANALUTO-0746	011	1-1670066-1	0		X	X	X	X	X	X	X	X	X	X	X									X		X			X	X			X		X		
N14 MAN 0720 F32	008	0-1670066-8	0		X	X	X	X	X	X	X	X	X	X	X									X		X	X		X	X			X		X		
DV6 Stage 3 0720	007	0-1670066-7	0	X	X			X	X	X	X						X	X	X	X	X			X	X	X			X			X		X	X		
DV6 Stage 4 0720	006	0-1670066-6	0	X	X			X	X	X	X			X		X	X	X	X	X	X			X	X	X	X			X			X		X		


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	16JUL2007	 TE Connectivity									
DIMENSIONS: mm		CHK	19JUL2007										
		G. PUCKEL											
		APVD	23JUL2007										
		G. MUMPER	NAME	DIFFERENT PIN OUT CONFIGURATION FOR 32 POS. MIXED RECEPTACLE HOUSING									
		PRODUCT SPEC											
		-											
		APPLICATION SPEC											
MATERIAL		ANGLES	114-18761-1	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO						
		FINISH	WEIGHT	A1	00779	 1670065	-						
		-	-	CUSTOMER DRAWING									
						SCALE	1:1	SHEET	5	OF	6	REV	027

PINOUT CONFIGURATION																																			
NOTES Bemerkungen	 MARKINGS FOR PINOUT- CONFIGURATION Markierung für Pinout- Konfiguration	 TE PN TE Nr.	REV	BLANKED CAVITIES INDICATE CLOSED LOCATIONS Leere Felder kennzeichnen geschlossene Kammern																															
				WITH "X" MARKED CAVITIES INDICATE OPEN LOCATIONS Markierte Felder mit "X" kennzeichnen offene Kammern																															
				1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32
-	099	9-1418392-9	0	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X		
HCM	005	0-1418392-5	0								X		X	X	X	X		X		X	X	X	X												

CODING 5

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-		-	SEE SHEET 1	-	-	-

CODING 5
COLOR BLUE
LEVER RIGHT
CABLE EXIT LEFT
PN 1418392

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	M. KRESSMANN	16JUL2007	 TE Connectivity													
DIMENSIONS: mm		CHK	G. PUCKEL	19JUL2007														
		TOLERANCES UNLESS OTHERWISE SPECIFIED :		APVD	NAME	DIFFERENT PIN OUT CONFIGURATION FOR 32 POS. MIXED RECEPTACLE HOUSING												
		0 PLC ± 0.1		G. MUMPER														
		1 PLC ± 0.1		PRODUCT SPEC														
		2 PLC ± 0.1		-														
		3 PLC ± 0.1		APPLICATION SPEC														
4 PLC ± 0.1		114-18761-1		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO										
MATERIAL		FINISH		WEIGHT		A1	00779	 1670065	-									
-		-		-		CUSTOMER DRAWING					SCALE	1:1	SHEET	6	OF	6	REV	027