





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	REVISED PER ECR-24-217119	04NOV2024	P.C	L.C

- 1 MATERIAL: HOUSING: POLYAMIDE, UL94V-2, WHITE
CONTACTS: BRASS, TIN-PLATED
- 2 FLAMMABILITY V2 FOR THICKNESS 0.38mm, 1.5mm, qnd 3.0mm PER IEC 60695-11-10.
- 3 GLOW-WIRE FLAMMABILITY (GWI) 800°C FOR THICKNESS 0.38mm AND 0.75mm PER IEC 60695-2-12.
- 4 GLOW-WIRE FLAMMABILITY (GWI) 960°C FOR THICKNESS 1.5mm AND 3.0mm PER IEC 60695-2-12.
- 5 GLOW-WIRE IGNITION (GWI) 825°C FOR THICKNESS 0.38mm, 0.75mm, 1.5mm AND 3.0mm PER IEC 60695-2-13.



2-1586863-4 SHOWN

24	46.2±0.2	[1.82±.01]	51.6	[2.03]	2-1586863-4
22	42.0±0.2	[1.65±.01]	47.4	[1.87]	2-1586863-2
20	37.8±0.2	[1.49±.01]	43.2	[1.70]	2-1586863-0
18	33.6±0.2	[1.32±.01]	39.0	[1.54]	1-1586863-8
16	29.4±0.2	[1.16±.01]	34.8	[1.37]	1-1586863-6
14	25.2±0.2	[.99±.01]	30.6	[1.21]	1-1586863-4
12	21.0±0.2	[.83±.01]	26.4	[1.04]	1-1586863-2
10	16.8±0.1	[.66±.00]	22.2	[.87]	1-1586863-0
8	12.6±0.1	[.50±.00]	18.0	[.71]	1586863-8
6	8.4±0.1	[.33±.00]	13.8	[.54]	1586863-6
4	4.2±0.1	[.17±.00]	9.6	[.38]	1586863-4
2	4.2±0.1	[.17±.00]	5.4	[.21]	1586863-2
POS	A		B±0.35[±.01]		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN K. WHITAKER 11JUL2007		 TE Connectivity					
			CHK C. CASH 11JUL2007							
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD C. CASH 11JUL2007		NAME				
		0 PLC ±		PRODUCT SPEC		RIGHT ANGLE HEADER, WITHOUT PEGS VAL-U-LOK(TM)				
		1 PLC ±		APPLICATION SPEC						
		2 PLC ± 0.5 [.02]								
		3 PLC ± 0.25 [.010]								
		4 PLC ± 0.150 [0059]								
		ANGLES ±								
MATERIAL 		FINISH		WEIGHT 0.000000		SIZE A2		CAGE CODE 00779	DRAWING NO C=1586863	RESTRICTED TO —
CUSTOMER DRAWING						SCALE		SHEET 1 of 1	REV D1	