


LOC
AP




DIST
-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
E		REV. BY ECO 09-027886	17DEC2009	HC	WLS
E1		REV. BY ECO 15-002213	11FEB2015	HC	WLS



- 1- CONTINUOUS STRIP ON REEL.
FITA CONTÍNUA EM BOBINA.
- 2- WIRE RANGE - 200/850 CMA
- 3- ALL UNSPECIFIED RADIUS 0,3 mm.
- 4- APPLICATION TOOLING KIT
FOR AMPLIVAR CONCEPT
ACC. TO TE SPECIFICATION.
- 5- BURRS MUST BE PRESENT ON SERRATIONS
AND ITS DIMENSIONS CONTROLLED ACCORDING
TO TE PROPRIETARY SPECIFICATION.



NONE	0,32 ±0,015mm. THK PH. BRONZE	1599721-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.C. CANTER 04MAY2005	TE Connectivity	
		CHK W.L. STEFANI 04MAY2005		
DIMENSIONS: mm		APVD -	NAME TAB RECEPTACLE, STATOR, AMPLIVAR	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC -	APPLICATION SPEC -	
0 PLC ±-		APVD -	SIZE A3	
1 PLC ±0,3		WEIGHT -	CAGE CODE 00779	DRAWING NO C=1599721
2 PLC ±0,13		RESTRICTED TO -		
3 PLC ±-		SCALE 5/1		
4 PLC ±-		SHEET 1 OF 1		
ANGLES ±1°		REV E1		
FINISH SEE TABLE		Customer Drawing		