


LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
AP	-	0 RELEASED	21NOV2005	VF	JAL
		A ECO-08-020033	18SEP2008	GO	WB

CAD
DO NOT REVISE EXCEPT BY CAD



① - SYNTHETIC INHIBITOR IN BOTH SIDES "C" MEMBER AND WEDGE MEMBER.


2 - APPLICABLE CABLE RANGE:

SUM OF DIA.		RUN WIRE		TAP WIRE		PART NUMBER
MAX.	MIN.	MAX.	MIN.	MAX.	MIN.	
22,76	18,75	17,37	15,24	12,70	4,11	1599790-1
27,01	22,77	17,37	15,24	14,27	6,55	1599790-2
31,22	27,02	17,37	15,24	15,24	8,23	1599790-3
34,75	31,21	17,37	15,24	17,37	11,68	1599790-4


① - INIBIDOR SINTÉTICO EM AMBOS OS LADOS DO COMPONENTE "C" E DO COMPONENTE CUNHA.

2 - FAIXA APLICÁVEL DE CABOS:

SOMA DOS DIÂMETROS		CONDUTOR PRINCIPAL		CONDUTOR DERIVAÇÃO		PART NUMBER
MAX.	MIN.	MAX.	MIN.	MAX.	MIN.	
22,76	18,75	17,37	15,24	12,70	4,11	1599790-1
27,01	22,77	17,37	15,24	14,27	6,55	1599790-2
31,22	27,02	17,37	15,24	15,24	8,23	1599790-3
34,75	31,21	17,37	15,24	17,37	11,68	1599790-4



ENGRAVING



1	-	-	-	5	30,1	ALUMINUM ALLOY	WEDGE MEMBER
-	1	-	-	4	34,0	ALUMINUM ALLOY	WEDGE MEMBER
-	-	1	-	3	37,7	ALUMINUM ALLOY	WEDGE MEMBER
-	-	-	1	2	41,0	ALUMINUM ALLOY	WEDGE MEMBER
1	1	1	1	1	—	ALUMINUM ALLOY	"C" MEMBER
-4	-3	-2	-1				
REQ. PER ASS'Y				ITEM	"A"	MATERIAL	DESCRIPTION
1599790							

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DWN: V. FUZZETTI 23NOV2005
 CHK: L. O. M. BORELLI 23NOV2005
 APVD: J. A. A. SALVIA 23NOV2005

TYCO ELECTRONICS do Brasil LTDA. Sao Paulo, Brasil

NAME: MEDIUM II ECONECT ASS'Y

PRODUCT SPEC: 108-37074-1
 APPLICATION SPEC: 411-37044-1

WEIGHT: -

SCALE: A2 00779 C=1599790

SHEET 1 OF 1 REV A