#### SAFETY ORGANIZATIONS

THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS HAVE BEEN MET:

UL RECOGNIZED: UL 1283 ESA CERTIFIED: CSA 22.2, # 0,0.4,8 VDE APPROVED: EN 133 200

#### OPERATING SPECIFICATIONS

LINE CURRENT/VOLTAGE: 15 AMP, 120/250 VAC, 10 AMP/40°C, 250 VAC

LINE FREQUENCY:

MAXIMUM LEAKAGE CURRENT,

9.5 µA @ 120V 50Hz 16.5 µA @ 250V 50Hz EACH LINE TO GROUND:

OPERATING AMBIENT TEMP. RANGE: -10°C TO +40°C @ RATED CURRENT, Ic.

IN AN AMBIENT, To, HIGHER THAN 40°C, THE MAXIMUM OPERATING CURRENT, Io, IS AS FOLLOWS:  $r = r - \sqrt{100 - r}$ 

100 - To  $I_0 = I_r$ 60

### RELIABILITY SPECIFICATIONS:

STORAGE TEMPERATURE: -40°C TO +85°C HUMIDITY: 21 DAYS @ 40°E 95% RH. CURRENT DVERLDAD TEST: 6 TIMES In FOR 8 SECONDS

CUSTOMER DRAWING CATALOG #15SRBS1-R EEN # | APPRVD. | DATE PJD 02MAY07

### TEST SPECIFICATIONS:

INDUCTANCE: N/A mH

CAPACITÀNCE: (MEASIRED @ 1KHz, 0.250VAC MAX., 25°C±1°C)
LINE TO GROUND: 100pF ± 20%

LINE TO LINE: DISCHARGE RESISTOR: N/A

L/G AND L/L I.R.

NO DISCHARGE RESISTOR:

6000M△ (MIN.) @ LOOVDE,


20°E AND 50% RH

# RECOMMENDED RECEIVING INSPECTION HIPOT:

LINE TO GROUND: 1500 VAC FOR 1 MINUTE 1450 VDC FDR 1 MINUTE LINE TO LINE:

#### FILTER APPROVAL

THE BEST WAY TO SELECT AND DUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.



50 <u>n</u> -	50a-50a(MINIMUM) INSERTION LOSS						
FREQUENCY HHz	1.0	5.0	10	50	100	300	
QB COWWON	/	/	/	3	6	22	
DIFF. dB	1	1	1	/	/	/	

THIRD ANGLE  $(\bigcirc)$ PROJECTION UNLESS OTHERWISE SPECIFIED. TOLERANCE TO BE ±.025 MATERIAL & FINISH: AS SUPPLIED

This document is proprietory to CORCOM INC and is not to be reproduced nor used for nonufocturing purposes except on CORCOM'S prior written consent.

TUCO Electronics ECOFCOM 620 S. BUTTERFIELD RD. HUNDELEIN IL 60060

## POWER LINE FILTER

	CAD FILE: G:\CD\15SRBS1\-ROQ YYCD # 2-6609987-0							
٠.	SCALE: ,	DATE:	CATALOG NO.	REV.				
	./5:1	LOMARO6	4500004 D	_				
	ORW. BY:	OR16:	15SRBS1-R	0				
_	ZD	PJO						