




LOC	DIST	REVISIONS					
A1	2	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B6	REVISED PER ECR-19-008967	30SEP2019	BDA	SF
			B7	REVISED PER ECR-24-224610	10MAR2025	AK	BR



- 1 MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK PLUG
- 2 RECOMMENDED PANEL THICKNESS 0.76 - 2.29 mm
- 3 PANEL MUST BE PUNCHED SO THAT THE HOUSING ENTERS THE PANEL IN THE SAME DIRECTION AS THE PUNCH
- 4 CIRCUIT NUMBER 1 LOCATION
- 5 DIMENSION INDICATED AS MOLDED. ADDITIONAL GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR
- 6 UNDERWRITERS RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE EACH ON SIDE OF HOUSING
- 7 MATERIAL CORRESPONDING TO THE REQUIREMENTS OF IEC 60335 (INCL. GLOW WIRE TEST 750°C, WITHOUT FLAME)
- 8 OPTIONAL FOR KEYING HOUSING IN PANEL
- 9 PRELIMINARY PART NOT RELEASED FOR PRODUCTION



1:1

OBSOLETE		1-1703062-2	A	PA66 UL94 V0 (GW T 750 °C)	NATURAL
		4-1703062-4	1	PA6 UL94 V0	NATURAL
		1703062-4	A	PA6 UL94 V2 GW T 750 °C	BLACK
		1703062-3	A	PA6 UL94 V2 GW T 750 °C	RED
		1703062-2	A	PA6 UL94 V2 GW T 750 °C	BLUE
		1703062-1	A	PA6 UL94 V2 GW T 750 °C	NATURAL
	REMARK	PN	REV	MATERIAL	COLOUR

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 16APR2004 CHK MAHNKE, B.		 TE Connectivity	
DIMENSIONS: mm		ZITZ, A. 26APR2004 APVD BLEICHER, M. 27APR2004			
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CAP 2 CIRCUIT UNIVERSAL MATE-N-LOK	
		0 PLC ± 1 PLC ± 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ±° MATERIAL FINISH			
		APPLICATION SPEC -			