



- Bemerkungen
NOTES
- 1 Massgebend ist der deutsche Text
ONLY THE GERMAN-LANGUAGE VERSION SHALL BE BINDING
 - 2 Lage des Kontaktpunktes auf der Leiterplatte; Abweichung ±0.4
POSITION OF CONTACT POINT ON BOARD; DEVIATION ±0.4
 - 3 Kontaktierung zur Drahtmitte um 0.7mm versetzt
CONTACTING 0.7mm DISPLACED TO WIRE CENTRELINE
 - 4 Kontaktkammer-Nr.
CONTACT CAVITY #
 - 5 Firmenlogo und Leergehäuse-Nr.
ARTWORK LOGO AND HOUSING # (NON LOADED)
 - 6 Vierkantloch 2x2 mm wahlweise Rastloch Ø2.5 mm
SQUARE HOLE 2x2 mm OPTIONAL LOCKING HOLE Ø2.5 mm
 - 7 Ausführung nach DIN 60249-2-4
BOARD DESIGN ACCORDING TO DIN 60249-2-4
 - 8 Crimp Kontakt-Nr.
Material: CuSn4 926770-1; 926917-1
CRIMP CONTACT # MATERIAL: CuSn4
 - 9 MATERIAL ACCORDING TO IEC-60335-1
(INCLUDING 750 °C NO FLAME)

B	0-1703133-5	MT-EDGE HOUSING	NATURAL	PA6	9
B	0-1703133-1	MT-EDGE HOUSING	NATURE	PA66	-
REV.	PART-NO.:	DESCRIPTION	COLOUR SIMILAR TO RAL #	MATERIAL	REMARKS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MAHNKE, B. 27SEP2004	TE Connectivity 9 POS. MT-EDGE HOUSING RAST 5mm		
DIMENSIONS: mm		CHK STREDAK, F. 20DEC2004			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD BLEICHER, M. 21DEC2004			
0 PLC ± 1 PLC ±0.2mm 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±° FINISH		PRODUCT SPEC 108-18003 APPLICATION SPEC 114-18002 WEIGHT 4.391 g			
MATERIAL PA6.6 / UL94V-2		CUSTOMER DRAWING	NAME	SIZE A2	RESTRICTED TO
			CAGE CODE	DRAWING NO. C-1703133	
			SCALE 5:1	SHEET 1 OF 1	REV B