




LOC	DIST	REVISIONS				
AF	50	P	LTR	DESCRIPTION	DATE	DWN
			1	PROPOSED	—	—

- 1 SPECIFICATIONS: MAGNET WIRE #34-#18 AWG
0.16[.006]mm-1.02[.040]mm DIA COPPER.
- 2 POCKET RECOMMENDATION: 1601431.
- 3 TERMINAL APPLICATION TO COMPLY WITH TYCO ELECTRONICS
SPECIFICATION NUMBER 114-13166 FIGURE 10, EXCEPT
SHOULDER IS 8.89 [.350] ABOVE THE TOP
OF THE POCKET (CAVITY).
- 4 1 MICRON [.000040] / 2 MICRONS [.000080] POST TIN PLATE.
- 5 TWO (2) TERMINALS SHOWN FOR ILLUSTRATION PURPOSES ONLY.
- 6 PRELIMINARY - NOT FOR PRODUCTION.



4	6	2-1601251-2
4	6	1601251-2
FINISH	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	JR RUTH	04NOV08	Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608		
		CHK	GENE JACONO	04NOV08			
DIMENSIONS: INCHES		APVD	GENE JACONO	04NOV08	NAME STANDARD RANGE WIRE TO 1.2 [.045] X 0.6 [.024] TAB SIAMEZE TERMINAL		
		PRODUCT SPEC	108-2085				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± 0.13 [.005] 4 PLC ± - ANGLES ± 2°		APPLICATION SPEC			SIZE	CAGE CODE	DRAWING NO
		FINISH			A2	00779	C=1601251
MATERIAL BRASS, 3/4 HARD		SEE TABLE	WEIGHT -		CUSTOMER DRAWING		
			SCALE 6:1		SHEET 1 of 1		REV 1