


DRAWING MADE IN AMERICAN PROJECTION



PDS. 1

OPTIONAL (2x)

SUPERSEDED BY 1-5161800-2

AMP



ORDER NUMBER	NUMBER OF POSITIONS	"L" MAX. M.M.	"L" MAX. INCH.
161800-2	2	5.0	.197
-3	3	7.5	.296
-4	4	10.0	.394
-5	5	12.5	.493
-6	6	15.0	.591
-7	7	17.5	.690
-8	8	20.0	.788
-9	9	22.5	.886
-10	10	25.0	.985
-11	11	27.5	1.083
-12	12	30.0	1.182
-13	13	32.5	1.280
-14	14	35.0	1.378
-15	15	37.5	1.477
-16	16	40.0	1.575
-17	17	42.5	1.674
-18	18	45.0	1.772
-19	19	47.5	1.871
2-161800-1	20	50.0	1.969
2-161800-3	23	57.5	2.264
2-161800-1	21	52.5	2.067

OBSOLETE

OBSOLETE

MATERIAL: HOUSING: P.B.T., 20% GLASS FILLED
CONTACT: PH.BE., TIN-LEAD (93/7) PLATED

△ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI



H1	ECO-09-025273	16NOV09	KK	AEG
LTR	REVISION	DATE	DR	APVD

SEE TABLE		SEE ABOVE		SEE ABOVE	
ORDER NO.		MATERIAL		PLATING	
CUSTOMER COPY FOR REFERENCE ONLY					
DR	PVT	DATE	17-4-81	©1977 BY AMP-HOLLAND N.V. ALL RIGHTS RESERVED AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.	
CRK		DATE		AMP-HOLLAND N.V. 's-Hertogenbosch	
DE		DATE		WIRE RANGE INSUL. RANGE FIRST USED	
SCALE		SIZE	NO	REV	
H7.2		B	C-161800	H1	
NAME: IN POS. FEMALE BARRER TO BARRER CONNECTOR ALSO FOR MINI MOUNT INTERCONNECTION SYSTEM. P/N: 2.5 MM.					

DIMENSIONS IN M.M. DO NOT SCALE PRINT DIMENSIONS THREE (3) IN INCHES

AMP 12804