

THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS					
HB		—		P	LTR	DESCRIPTION	DATE	DWN	APVD
					E	REMOVED THE RIB ON THE BASE TO CASE ECO-15-011310	04-Dec-15	YS.HHL	C
					E1	NEW ADD PN ECO-17-004477	22-Jan-18	WQ.Y	K.T





Diagram dimension	Tolerance
0.99mm max.	±0.1mm
1 - 2.99mm	±0.2mm
3mm min.	±0.3mm




FIGURE FOR PRINTED CIRCUIT BOARD PROCESSING
(BOTTOM VIEW)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -
MATERIAL	FINISH
-	-

DWN	Hu.XieLi
CHK	Mak.Simon
APVD	Mingjung.Ho
PRODUCT SPEC	-
APPLICATION SPEC	-
WEIGHT	-
CUSTOMER DRAWING	

TE Connectivity	
NAME	
OJE CUSTOMER DRAWING(OJE-SS-LMH2)	
SIZE	CAGE CODE
A3	00779
DRAWING NO	1721261
RESTRICTED TO	-
SCALE	5:1
SHEET	1 of 2
REV	E1

LOC	DIST	REVISIONS					
		P	LYR	DESCRIPTION	DATE	DWN	APV
HB	—		—	SEE SHEET 1	—	—	

E	1721261-7	QJE-SS-112LMH2	12V	QJE-SS-112LMH2	g
	1721261-6	QJE-SS-124LMH2	24V	QJE-SS-124LMH2	f
	1721261-5	QJE-SS-112LMH2	12V	QJE-SS-112LMH2	e
	1721261-4	QJE-SS-109LMH2	9V	QJE-SS-109LMH2	d
	1721261-3	QJE-SS-106LMH2	6V	QJE-SS-106LMH2	c
	1721261-2	QJE-SS-105LMH2	5V	QJE-SS-105LMH2	b
	1721261-1	QJE-SS-103LMH2	3V	QJE-SS-103LMH2	a
	TE PART NO	PART A	PART B	DESCRIPTION	TYPE

RELAY TYPE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Hu.XieLi	 TE Connectivity		INDUSTRY/STABILITY		TOLERANCE		MATERIAL		DESCRIPTION		ITEM			
DIMENSIONS: mm		CHK Mak.Simon			NAME		OJE CUSTOMER DRAWING(OJE-SS-LMH2)		APPLICATION SPEC		SIZE		CAGE CODE		DRAWING NO	
		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD Mingjung.Ho	PRODUCT SPEC -		APPLICATION SPEC -		A3		00779		 1721261		-		
MATERIAL -		FINISH -	WEIGHT -		CUSTOMER DRAWING		SCALE 5:1		SHEET 2 of 2		REV F1					