

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- - -


© COPYRIGHT - By - TE CONNECTIVITY

ALL RIGHTS RESERVED.




LOC  
HBDIST  
-

REVISIONS

| P | LTR | DESCRIPTION                                       | DATE      | DWN | APVD |
|---|-----|---------------------------------------------------|-----------|-----|------|
| E |     | REMOVED THE RIB ON THE BASE TO CASE ECO-15-011310 | 04DEC2015 | HYS | CHL  |



CONNECTION DIAGRAM(3/1)



| Diagram dimension | Tolerance |
|-------------------|-----------|
| 0.99mm max.       | ±0.1mm    |
| 1 - 2.99mm        | ±0.2mm    |
| 3mm min.          | ±0.3mm    |

|                                        |  |                  |          |       |                                                 |           |            |
|----------------------------------------|--|------------------|----------|-------|-------------------------------------------------|-----------|------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN              | Fu.Bo    | -     | TE Connectivity                                 |           |            |
| DIMENSIONS:<br>mm                      |  | CHK              | XN.ZHANG | -     |                                                 |           |            |
|                                        |  | APVD             | CH.HSU   | -     | NAME<br>OJE-SH-112LMH SPEC 000 CUSTOMER DRAWING |           |            |
|                                        |  | PRODUCT SPEC     | -        | -     |                                                 |           |            |
| MATERIAL<br>-                          |  | APPLICATION SPEC | -        | -     | SIZE                                            | CAGE CODE | DRAWING NO |
|                                        |  | WEIGHT           | -        | -     | A3                                              | 00779     | C= 1721870 |
| FINISH<br>-                            |  | CUSTOMER DRAWING |          | SCALE | 5:1                                             | SHEET     | 1 OF 2     |
|                                        |  |                  |          | REV   | E                                               |           |            |

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , - .

© COPYRIGHT - By - TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC  
HB

DIST

-

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

-

SEE SHEET 1

-

-

-

|            |                    |        |                |      |
|------------|--------------------|--------|----------------|------|
| 1721870-5  | OJE-SH-112LMHF,000 | 12V    | OJE-SH-112LMHF | a    |
| TE PART NO | DESCRIPTION        | PART B | PART A         | TYPE |

RELAY TYPE

NOTES:

1.TERMINAL DIMENSION BEFORE TINNING.

② 2.LOT NO. SYSTEM AS FOLLOWING:

WEEK  
YEAR

③ 2.TERMINAL DIMENSION IS BEFORE SOLDER DIP;

③ 3.FOR THE TIN-PLATING OF THE PINS:

+0.1mm FOR WIDTH,THICKENSS AND DIAMETER.

+0.5mm FOR LENGTH.

④③ 4.MARKING FROM INK TO LASER AND USING WELDING CONTACT

⑤ 5.ADD LOT NO. SYSTEM AS FOLLOWING;



I, DIGITS FOR DAY OF THE WEEK

1...MONDAY IN THIS WEEK;

2...TUESDAY IN THIS WEEK;

.....

7...SUNDAY IN THIS WEEK

II, DIGITS FOR SHIFT OF THE DAY

1...DAY SHIFT IN THIS DAY;

2...NIGHT SHIFT IN THIS DAY;

III, ONE CHARACTER DISTINGUISH THE LINE IDENTITY, SUCH AS: A,B,....Z

|                  |            |             |                      |      |
|------------------|------------|-------------|----------------------|------|
|                  |            | UV GLUE     | SEAL (VENT HOLE)     | 16   |
|                  |            | EPOXY RESIN | SEAL (BASE & BOBBIN) | 15   |
|                  |            | MW79        | MAGNETIC WIRE        | 14   |
| 94V-0            |            | P.B.T       | CASE                 | 13   |
| 94V-0            |            | P.B.T       | BASE                 | 12   |
| 94V-0            |            | NYLON       | BOBBIN               | 11   |
|                  | SOLDER DIP | C.P WIRE    | COIL TERMINAL        | 10   |
| 94V-0            |            | P.P.S       | CARD                 | 9    |
|                  |            | Ag ALLOY    | MOVABLE CONTACT      | 8    |
|                  |            | Ag ALLOY    | NO.CONTACT           | 7    |
|                  |            | STEEL       | HINGE SPRING         | 6    |
|                  | SOLDER DIP | PBP         | NO.TERMINAL          | 5    |
|                  | SOLDER DIP | PBS         | MOVABLE SPRING       | 4    |
|                  | NIP        | STEEL       | CORE                 | 3    |
|                  | NIP        | STEEL       | ARMATURE             | 2    |
|                  | NIP        | STEEL       | YOKE                 | 1    |
| INCOMBUSTIBILITY | TREATMENT  | MATERIAL    | DESCRIPTION          | ITEM |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

Fu.Bo

CHK

XN.ZHANG

APVD

CH.HSU

PRODUCT SPEC

-

APPLICATION SPEC

-


WEIGHT

-

CUSTOMER DRAWING

DIMENSIONS:

mm



0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

FINISH

TOLERANCES UNLESS

OTHERWISE SPECIFIED:

± -

± -

± -

± -

± -

± -

± -

MATERIAL

-

FINISH

-

DWN

Fu.Bo

CHK

XN.ZHANG

APVD

CH.HSU

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME

OJE-SH-112LMH SPEC 000 CUSTOMER DRAWING

SIZE

CAGE CODE

DRAWING NO

1721870

RESTRICTED TO

-

A3

00779

C=

1721870

SCALE 5:1

SHEET 2 OF 2

REV E