





P	LTR	DESCRIPTION	DATE	DWN	APVD
	E1	REVISED PER ECR-22-159057	23NOV2022	HS	SZ



RECOMMENDED P.C.BOARD LAYOUT(T=1.6)

(TOP VIEW)(TOLERANCE:±0.05)

NOTE:

1. MATERIAL:

△3 HOUSING: PBT(SOLDER CAPABLE,UL 94-V0,COLOR:SEE TABLE.)

④ HOUSING: PA9T(REFLOW CAPABLE,UL 94-V0,COLOR:SEE TABLE.)

CAP: LCP(REFLOW CAPABLE,UL 94-V0,COLOR:BLACK.)

BACK STOPPER: PBT(SOLDER CAPABLE,UL 94-V0,COLOR:BLACK.)

CONTACT: PHOSPHOR BRONZE, THICKNESS =0.25mm.

SHIELD: STAINLESS STEEL, THICKNESS=0.30mm.

2. FINISH:

CONTACT:GOLD FLASH OVER

0.762um[30u"]MIN. PALLADIUM-NICKEL OR ALTERNATIVE

0.76mm[30m"] MIN.GOLD PLATED ON CONTACT
2.54um[100u"]MIN. MATTE TIN ON SOLDER TAIL


2.54 μ m[100u"]MIN. MATTE-TIN ON SOLDER TAILS,
1.27 μ m[50u"]MIN. NICKEL. UNDERPLATED ALL OVER.

D: 2.54um [100u"] MIN. TIN PLATED OVER

1.27um [50u"] MIN. NICKEL UNDERPLATED

△ 6 SHIELD: 0.762-2.03um [30-80u"] SOLDERABLE NICKEL
OVER 0.762-2.03um [30-80u"] COPPER

SEE SHEET 4	BLACK	1734366-5		
SEE SHEET 5	BLACK	1734366-4		
	BLUE	1734366-3		
SEE SHEET 4	WHITE	1734366-2		
	BLACK	1734366-1		
PACKING	HSG'S COLOR	PART NUMBER	HOUSING MATERIAL	SHIELD FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CHIEN 19SEP2008		 TE Connectivity	
		CHK S. CHIEN 19SEP2008			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.38 1 PLC ± 0.25 2 PLC ± 0.13 3 PLC ± 0.05 4 PLC ± — ANGLES ± 2°		NAME RECEPT ASSY,VERTICAL,4POSITION THRU-HOLE,TYPE A USB —	
		PRODUCT SPEC 108-57547			
		APPLICATION SPEC 501-57635			
MATERIAL SEE NOTES		WEIGHT 1.82 GRAMS		SIZE A3	CAGE CODE 000779
FINISH SEE NOTES		CUSTOMER DRAWING		DRAWING NO C-1734366	RESTRICTED TO —
				SCALE 1:1	SHEET 1 OF 6
				REV F1	


4

3



2

1


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—





1734366-6 AS SHOW
OTHER DIMENSIONS ARE THE SAME AS SHEET1





SEE SHEET 6	BLACK	1734366-6	△	△
PACKING	HSG'S COLOR	PART NUMBER	HOUSING MATERIAL	SHIELD FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CHIEN 19SEP2008	 TE Connectivity		
		CHK S. CHIEN 19SEP2008			
DIMENSIONS: mm		APVD W.KODAMA PRODUCT SPEC	NAME RECEPT ASSY,VERTICAL,4POSITION THRU-HOLE,TYPE A USB —		
		108-57547			
		APPLICATION SPEC			
		501-57635	SIZE	CAGE CODE	DRAWING NO
MATERIAL SEE NOTES		WEIGHT 1.82 GRAMS	A3	00779	C-1734366
		CUSTOMER DRAWING		SCALE 1:1	SHEET 2 OF 6
				REV E1	


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



1734366-7 AS SHOW
OTHER DIMENSIONS ARE THE SAME AS SHEET1



SEE SHEET 4	BLACK	1734366-7	△	△
PACKING	HSG'S COLOR	PART NUMBER	HOUSING MATERIAL	SHIELD FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CHIEN 19SEP2008	 TE Connectivity		
		CHK S. CHIEN 19SEP2008			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD W.KODAMA	NAME RECEPT ASSY,VERTICAL,4POSITION THRU-HOLE,TYPE A USB		
	0 PLC ± 0.38 1 PLC ± 0.25 2 PLC ± 0.13 3 PLC ± 0.05 4 PLC ± — ANGLES ± 2°	PRODUCT SPEC 108-57547			
MATERIAL SEE NOTES	FINISH SEE NOTES	APPLICATION SPEC 501-57635	SIZE A3	CAGE CODE 00779	DRAWING NO C-1734366
		WEIGHT 1.82 GRAMS			RESTRICTED TO —
		CUSTOMER DRAWING	SCALE 1:1	SHEET 3 OF 6	REV E1

© 2021TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

USE THE TAPE TO FIX THE TRAY(4X)

TRAY

120 PCS/TRAY

VIEW B:

VIEW B

20.0

20.0

25.0

342.5

INNER BOX(10 TRAY)
TOTAL:1200 PCS

270

360

220

OUT BOX

375

560

240

1470-19 (1/08)

CARTON

20 TRAYS/CARTON
TOTAL:2400PCS
GROSS WEIGHT:7.2KGS
NET WEIGHT:5.6KGS

UPPER COVER

LOWER COVER

NOTE :

1. PACKAGING MATERIAL IN PLASTIC, RUBBER,INK,PIGMENT AND PAINT
MUST MEET CONTROLLED SUBSTANCES SPEC PER 230-702.
* CADMIUM AND CADMIUM COMPOUNDS NOT TO EXCEED:5 PPM.
* LEAD,CADMIUM,CHROM VI AND MERCURY NOT TO EXCEED:100 PPM(COMBINED).

2. MATERIAL :
TRAY: PS, UPPER COVER THICKNE=0.5MM.
LOWER COVER THICKNE=0.7MM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

0 PLC ± 0.38

1 PLC ± 0.25

2 PLC ± 0.13

3 PLC ± 0.05

4 PLC ± -

ANGLES ± 2°

FINISH

SEE NOTES

DWN S. CHIEN 19SEP2008

CHK S. CHIEN 19SEP2008

APVD W.KODAMA

PRODUCT SPEC 108-57547

APPLICATION SPEC 501-57635

WEIGHT 1.82 GRAMS

CUSTOMER DRAWING

TE

TE Connectivity

RECEPT ASSY,VERTICAL,4POSITION
THRU-HOLE,TYPE A USB

SIZE A3

CAGE CODE 00779

DRAWING NO C-1734366

RESTRICTED TO


SCALE 1:1

SHEET 5 OF 6

REV E1




1470-19 (1/15)

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



NOTE :

1. PACKAGING MATERIAL IN PLASTIC, RUBBER,INK,PIGMENT
AND PAINT
MUST MEET CONTROLLED SUBSTANCES SPEC PER 230-702.
* CADMIUM AND CADMIUM COMPOUNDS NOT TO EXCEED:5 PPM.
* LEAD,CADMIUM,CHROM VI AND MERCURY NOT TO
EXCEED:100 PPM(COMBINED).
2. MATERIAL :
REEL:BLACK CONDUCTIVE POLYSTYRENE ALLOY



OUT BOX PACKAGE DIAGEAM DRAWING

1440	1734366-6
QTY	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CHIEN 19SEP2008		 TE Connectivity	
DIMENSIONS: mm		CHK S. CHIEN 19SEP2008			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD W.KODAMA		NAME	
		PRODUCT SPEC 108-57547		RECEIPT ASSY,VERTICAL,4POSITION THRU-HOLE,TYPE A USB	
0 PLC ± 0.38 1 PLC ± 0.25 2 PLC ± 0.3 3 PLC ± 0.05 4 PLC ± - ANGLES ± 2°		APPLICATION SPEC 501-57635		SIZE	RESTRICTED TO
MATERIAL SEE NOTES		WEIGHT 1.82 GRAMS		CAGE CODE A300779	DRAWING NO C-1734366
FINISH SEE NOTES		CUSTOMER DRAWING		SCALE 1:1	SHEET 6 OF 6
				REV F1	