














” WITH SHELL ”

OBSOLETE	TUBE	YELLOW (PMS 114C)	50μ"	3-1734460-4
			30μ"	3-1734460-3
			15μ"	3-1734460-2
OBSOLETE			TRAY	YELLOW (PMS 114C)
	50μ"	2-1734460-4		
	30μ"	2-1734460-3		
	15μ"	2-1734460-2		
	 BLACK	6μ"		2-1734460-1
		50μ"		1734460-8
		30μ"		1734460-7
		15μ"		1734460-6
	BLACK	6μ"		1734460-5
		50μ"		1734460-4
		30μ"		1734460-3
		15μ"		1734460-2
	6μ"	1734460-1		
PACKAGE	HSG. COLOR	MIN. GOLD THICKNESS	PART NUMBER	



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN O, HU 300CT2006		TE Connectivity					
		CHK S, HOU 300CT2006							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± 0.3 2 PLC ± 0.2 3 PLC ± 0.15 4 PLC ± — ANGLES ± 3°		APVD W, J, KE 300CT2006		NAME			
				PRODUCT SPEC 108-57527		MODULAR JACK RJ45, MULTI-PORT SHIELDED, THRU-HOLE, RIGHT ANGLE —			
				APPLICATION SPEC —					
MATERIAL —		FINISH —		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
				A3		00779	C-1734460	—	
WEIGHT 22 GRAMS									
CUSTOMER DRAWING							SCALE 1:1	SHEET 1 OF 4	REV F

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



RECOMMENDED PCB LAYOUT (THICKNESS: 1.6mm)
(TOP VIEW) (TOLERANCE:±0.05)



NOTE:

1. MATERIAL:
HOUSING: PBT WITH 30% GF, UL 94V-0, COLOR: SEE TABLE.
CONTACTS: PHOSPHOR BRONZE.
2. FINISH:
CONTACTS: GOLD PLATED (SEE TABLE) ON CONTACT AREA,
1.27µm [50µ"] MIN. NICKEL UNDERPLATED ALL OVER.
3. WAVE SOLDER CAPABLE TO 240°C PER TYCO TEST SPEC.
109-202, CONDITION A.


” WITHOUT SHELL ”

OBSOLETE	YELLOW (PMS 114C)	50μ"	1=1734460=8
		30μ"	1=1734460=7
		15μ"	1=1734460=6
		6μ"	1=1734460=5
	BLACK	50μ"	1=1734460=4
		30μ"	1=1734460=3
		15μ"	1=1734460=2
		6μ"	1=1734460=1
	HSG. COLOR	MIN. GOLD THICKNESS	PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN O, HU	300CT2006	TE Connectivity		
		CHK S, HOU	300CT2006			
		APVD W, J, KE	300CT2006	NAME		
		PRODUCT SPEC 108-57527		MODULAR JACK RJ45, MULTI-PORT SHIELDED, THRU-HOLE, RIGHT ANGLE		
		APPLICATION SPEC		—		
		—	—	SIZE	CAGE CODE	DRAWING NO
		WEIGHT	22 GRAMS	A3	00779	C-1734460
		CUSTOMER DRAWING			SCALE	SHEET
					1:1	2 OF 4
					REV	E



10 Kg	8 Kg	60	8	480 PCS	1-1734460-X
13 Kg	11 Kg	60	8	480 PCS	2-1734460-X
					1734460-X
GROSS WEIGHT	NET WEIGHT	PCS/TRAY	TRAYS /CARTON	QUANTITY	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN O, HU300CT2006		TE Connectivity			
		CHK S, HOU300CT2006					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± 0.3 2 PLC ± 0.2 3 PLC ± 0.15 4 PLC ± - ANGLES ± 3°		NAME MODULAR JACK RJ45, MULTI-PORT SHIELDED, THRU-HOLE, RIGHT ANGLE -			
							
MATERIAL -		FINISH -		SIZE A3	CAGE CODE 00779	DRAWING NO C=1734460	RESTRICTED -
CUSTOMER DRAWING				SCALE 1:1	SHEET 3 OF 4	REV F	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



13 Kg	11 Kg	9	50	450 PCS	3-1734460-X
GROSS WEIGHT	NET WEIGHT	PCS/TUBE	TUBES /CARTON	QUANTITY	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN O, HU	300CT2006	 TE Connectivity		
		CHK S, HOU	300CT2006			
		APVD W, J, KE	300CT2006	NAME		
		PRODUCT SPEC	108-57527	MODULAR JACK RJ45, MULTI-PORT SHIELDED, THRU-HOLE, RIGHT ANGLE		
		APPLICATION SPEC	—	—		
		WEIGHT	22 GRAMS	SIZE	CAGE CODE	DRAWING NO
		CUSTOMER DRAWING		A3	00779	C-1734460
		SCALE	1:1	SHEET	4 OF 4	REV E