







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	21NOV2014	AP	RP

- 1 0.76µm MIN GOLD OVER 1.27µm MIN NICKEL OR GOLD FLASH OVER 0.76µm MIN PALLADIUM-NICKEL OVER 1.27µm MIN NICKEL
- 2 0.76µm MIN TIN OVER 1.27µm MIN NICKEL
- 3 MATERIAL:
CONTACT - COPPER ALLOY
SHIELD - PHOSPHOR BRONZE
HOUSING - LCP, UL94V-0
CHICKLET - GLASS FILLED POLYESTER
- 4 REFERENCE APPLICATION SPEC 114-13020 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.
- 5 DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.
- 6 SEATING HEIGHT TO BOARD SURFACE.
- 7 CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
- 8 DATE CODE
- 9 OPTIONAL POWER CONTACT PN 535875-X
- 10 PART NUMBER



DETAIL B
SCALE 10:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AJITH PAI 21NOV2014	TE Connectivity		
DIMENSIONS: mm		CHK R. PATTERSON 21NOV2014			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. PATTERSON 21NOV2014	NAME RECEPTACLE ASSEMBLY, 30 POSITION RIGHT HAND, 6 ROW, DUAL BEAM, Z-PACK HS3 PLUS		
0 PLC ± 1 PLC ±0.5 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ± FINISH		PRODUCT SPEC 108-1957 APPLICATION SPEC 114-13020 WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C-1645680
MATERIAL		Customer Drawing	SCALE 3:1	SHEET 1 OF 2	REV A

D

D

C


C

B

B

A

A



RECOMMENDED PRINTED
CIRCUIT BOARD LAYOUT
COMPONENT SIDE OF PRINTED CIRCUIT BOARD

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AJITH PAI 21NOV2014	TE Connectivity	
DIMENSIONS: mm		CHK R. PATTERSON 21NOV2014		
		APVD R. PATTERSON 21NOV2014		NAME RECEPTACLE ASSEMBLY, 30 POSITION RIGHT HAND, 6 ROW, DUAL BEAM, Z-PACK HS3 PLUS
		PRODUCT SPEC 108-1957		SIZE A2
MATERIAL		APPLICATION SPEC 114-13020		CAGE CODE 00779
		WEIGHT -		DRAWING NO C-1645680
		Customer Drawing		RESTRICTED TO -
		SCALE 3:1		SHEET 1 OF 2
				REV A