





LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION		DATE	DWN	APVD
	B1	REVISED PER ECO-11-005301		07MAR11	RK	HMR



NOTE:
1.MATERIAL:
HOUSING: THERMOPLASTIC WITH 30% G/F, UL 94V-0, NATURE COLOR.
CONTACTS: PHOSPHOR BRONZE.
TABS:BRASS.
2.FINISH:
CONTACT: 3.048μm (120μ") MIN. MATTE-TIN OVER
1.27μm (50μ") MIN. NICKEL ON ENTIRE CONTACT.
TABS: 3.048μm (120μ") MIN. MATTE-TIN OVER
1.27μm (50μ") MIN. NICKEL ON ENTIRE CONTACT.
3.REFLOW SOLDER CAPABLE TO 260°C PER TE CONNECTIVITY SPEC.
109-201, CONDITION B.
4.NO TE LOGO AND DATE CODE ON THE PRODUCT.
5.PART NO. OF RECEPTACLE CONTACT & HOUSING (BASE NO.#):
1734597 & 1470364.
△NO ACCUMULATE TOLERANCE.

OBSOLETE

0.21g	15.50	17.30	14.00	15	1-1734709-5
0.20g	14.50	16.30	13.00	14	1-1734709-4
0.19g	13.50	15.30	12.00	13	1-1734709-3
0.17g	12.50	14.30	11.00	12	1-1734709-2
0.16g	11.50	13.30	10.00	11	1-1734709-1
0.15g	10.50	12.30	9.00	10	1-1734709-0
0.14g	9.50	11.30	8.00	9	1734709-9
0.12g	8.50	10.30	7.00	8	1734709-8
0.11g	7.50	9.30	6.00	7	1734709-7
0.10g	6.50	8.30	5.00	6	1734709-6
0.09g	5.50	7.30	4.00	5	1734709-5
0.08g	4.50	6.30	3.00	4	1734709-4
0.07g	3.50	5.30	2.00	3	1734709-3
0.05g	2.50	4.30	1.00	2	1734709-2
WEIGHT	C	B	A	NO. OF CONTACTS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN F. YANG 10APR2009	TE Connectivity		
		CHK S. CHIEN 10APR2009			
		APVD W. KODAMA 10APR2009			
		PRODUCT SPEC 108-57264			
QUALIFICATION TEST REPORT 501-57283		WEIGHT SEE TABLE	SIZE A3	CAGE CODE 00779	DRAWING NO C-1734709
CUSTOMER DRAWING		SCALE -	SHEET 1 OF 3	REV B1	

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

BY

ALL RIGHTS RESERVED.

LOC

DW

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1.	—	—	—

W±0.4

ø330

ADHESIVE TAPE

4 PLC

LABEL

160 MIN.

PEELING ANGLE

165° ~ 180°

ABOUT 160 MM LONG

UNLOADED SECTION

PRODUCT LOADING SECTION

ABOUT 230 MM LONG

UNLOADED SECTION

PULL OUT DIRECTION

PARTITION

TAPE & REEL

VOID FILLER

BAG

PARTITION

CARTON

DIMENSIONS:

340 X 340 X 250

2.00

4.00

ø1.50

3.35

W±0.30

12.00

1.50

1.70

CARRIER FOR 15 PIN

2.00

4.00

ø1.50

3.35

W±0.30

12.00

PIN 1#

CARRIER FOR 2 TO 5 PIN & 7 TO 14 PIN

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC

QUALIFICATION TEST REPORT

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:

MM

0 PLC

±

—

1 PLC

±

—

2 PLC

±

—

3 PLC

±

—

4 PLC

±

—

ANGLES

±

—

FINISH

SEE NOTE

TE Connectivity

WIRE TO BOARD CONNECTOR

SIDE ENTRY, SINGLE ROW, SMT TYPE

SIZE

A3

CAGE CODE

00779

DRAWING NO

C=1734709

RESTRICTED TO

SCALE

—

SHEET

2 OF 3

REV

B1

1470-19 (3/11)

