






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B6	REVISED PER ECR-25-243298	07MAY2025	MK	MS




SECTION A-A

NOTES:

- 1 MATERIAL : PHOSPHOR BRONZE, THICKNESS : 0.20mm
- 2 FINISH : SEE TABLE
- 3. ACCEPTS HOUSING : 1735447, 2041423
- 4. APPLICABLE WIRES : AWG #30~#24
- 5. INSULATION O.D. : 0.9 TO 1.5mm
- 6. ADDED CHECK POINTS(P1,P2,P3) TO MEASURE PLATING THICKNESS AFTER STAMPING




SECTION B-B



SECTION C-C

PART NO.	FINISH
1735801-1	80μ" MIN. PRE-TIN PLATED OVER 50u" MIN. NICKEL PLATED
1735801-2	100μ" MIN. PRE-MATTE TIN PLATED OVER 50μ" MIN. NICKEL PLATED
1735801-3	1μ" to 3μ" Gold plating on contact area, 1.27um min Nickel under-plate overall

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN YMLEE	28APR2009	 TE Connectivity		
		CHK VTAN	18MAR2011			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD SFEONG	18MAR2011	NAME 2.0MM PITCH HPI CRIMP CONTACT		
		PRODUCT SPEC 108-51087				
	0 PLC ± - 1 PLC ± 0.3 2 PLC ± 0.3 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH	APPLICATION SPEC 114-57011		SIZE A3	CAGE CODE 00779	DRAWING NO C-1735801
		WEIGHT 0				
MATERIAL 1	FINISH 2	CUSTOMER DRAWING		SCALE 3:1	SHEET 1 OF 1	REV B6