




DO NOT SCALE
DIMENSIONS IN mm

METRIC


THIRD ANGLE
PROJECTION

NOTES:

- 1 REVERSE REELING FOR USE WITH MINI-APPLICATOR.
- 2 CRIMPING SPECIFICATION 114-25003.
- 3 PREPLATED STOCK 0,8µm MIN. GOLD ON CONTACT AREA OVER 1,25µm MIN. NICKEL OVERALL. ZONE I: 0,5µm MIN. GOLDFLASH.
- 4 PREPLATED STOCK 0,8µm MIN. GOLD ON CONTACT AREA OVER 1,25µm MIN. NICKEL OVERALL. GOLDFLASH ON REMAINDER (GOLD FLASH IS NOT MANDATORY ON THE PILOTED CARRIER STRIP).
- 5 WIRE RANGE: 28-32 AWG.
- 6 SPLICING - MAXIMUM 1 LOOSE END PER REEL IS ALLOWED



SECTION A-A
SCALE 20:1



SECTION B-B
SCALE 20:1

		SEL. Au/Au FLASH	4	167023-2	167020-2
		SEL. Au/Au FLASH	3	167023-1	167020-1
		FINISH		LOOSE PIECE NR.	PARTNUMBER
				CUSTOMER DRAWING FOR REFERENCE ONLY WILL NOT BE UPDATED	
				© COPYRIGHT 19- BY AMP HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED.AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.	
				THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION 19	
C	STANDARDIZATION OF PLATING & SPLICING	GVP	KJK	30JUL2024	AMP HOLLAND B.V. 's-Hertogenbosch, The Netherlands.
B	EH-2039-98	JvL	JvL	03-12-98	
A	EH-0491-93	JvdH	D.S.	10-07-93	
LTR.	REVISION RECORD	DR.	CHK.	DATE	AMP MODU MOD. IV RECEPTACLE, STRIP.
DR.: J.V.D.HEIJDEN	CHK.: J.V.LIEMPT	APP.: E.LEIJTENS	DWG.No.		
DATE: 10-07-93	DATE: 19-07-93	DATE: 19-07-93	C-167020	REV.LTR.	SHEET
				C	1 OF 1

A

B

C

D

E

F

G