

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.


LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
	0	CONVERTED RADIALL DWG TO TYCO ACAD DWG	11/03	-	-		
	1	REVISED	22APR10	RF	JM		

1 FRONT & REAR INSULATORS: THERMOSET EPOXY PER ASTM D5948  
 CONTACT RETENTION CLIPS: COPPER ALLOY PER ASTM B194



2 DATE CODE: YEAR & WEEK (YYWW)

3. DESCRIPTIVE PART NUMBER: GPRAN09PA  
 6 CAVITIES FOR SIZE 16 PIN CONTACTS  
 3 CAVITIES FOR SIZE 20 PIN CONTACTS

4. THIS PRODUCT IS SOLD BY TYCO ELECTRONICS UNDER A LICENSE FROM RADIALL SA.



MATING FACE



THIS PRINT IS  
**PRELIMINARY**  
 UNQUALIFIED PRODUCT  
 CONTACT PRODUCT ENGINEERING  
 BEFORE USING THIS PRINT

1738062-1  
 PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	NOV03	Tyco Electronics Corporation	
DIMENSIONS: mm [INCHES]		R FLAIG	NOV03	Harrisburg, PA 17105-3608	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	NOV03	NAME	
0 PLC ± -		J MOSIER	NOV03	GPR-A PIN INSERT, CLASS N, CONTACT ARRANGEMENT 09	
1 PLC ± -		APVD	NOV03	SIZE	CAGE CODE
2 PLC ± 0.05 [.002]		J MOSIER	NOV03	A2	00779
3 PLC ± -		PRODUCT SPEC		DRAWING NO	RESTRICTED TO
4 PLC ± -		APPLICATION SPEC		C=1738062	-
ANGLES ± -		WEIGHT	-	SCALE	SHEET
FINISH		CUSTOMER DRAWING		1:1	1 OF 1
MATERIAL				REV	1