





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	B	REV PER ECO 10-026412	1-5-11	CT KH



MATING FACE



1 FRONT & REAR INSULATOR: HIGH-TEMP THERMOPLASTIC OR THERMOSET EPOXY PER ASTM D5948.  
 CONTACT RETENTION CLIPS: STAINLESS STEEL PER AISI 302 OR COPPER ALLOY PER ASTM B194  
 REAR GROMMET & INTERFACIAL SEAL: FLUROSILICONE ELASTOMER PER MIL-R-25988 B, EXCEPT 4.6.6.1

2 PART TO BE MARKED WITH TE IDENTIFICATION, TE PART NO. AND DATE CODE: YEAR & WEEK (YY WW) IN APPROXIMATE AREA SHOWN.

3. THIS INSERT CONTAINS: 3 CAVITIES FOR SIZE 5 PIN CONTACTS

4. THIS PRODUCT IS SOLD BY TYCO ELECTRONICS UNDER A LICENSE FROM RADIAL SA.

ENVIRONMENTAL	GPRBEC3PA	1738086-1
REMARKS	DESCRIPTIVE PART NO.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN	BH	12 JUL 06	Tyco Electronics Harrisburg, PA 17105-3608
DIMENSIONS:		CHK	JPM	12 JUL 06	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	JPM	12 JUL 06	
mm		PRODUCT SPEC		NAME	
0 PLC ±-		APPLICATION SPEC		SIZE	
1 PLC ±0.1		WEIGHT		CAGE CODE	
2 PLC ±0.05		CUSTOMER DRAWING		DRAWING NO.	
3 PLC ±-		SCALE 4:1		RESTRICTED TO	
4 PLC ±-		SHEET 1 OF 1		REV B	
ANGLES ±-		REV B			
FINISH ±1					