



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - BY - ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
	B	REVISED PER ECO-12-018187	5NOV2012	CT	KH		





MATING FACE

INTERFACIAL SEAL (-1 ONLY)



GROMMET (-1 & -3 ONLY)



THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING

REMARKS	DESCRIPTIVE PART NO.	PART NUMBER
NON-ENV	GPRBN06PB	1738101-4
GROMMET ONLY	GPRBH06PB	1738101-3
ENVIRONMENTAL	GPRBE06PB	1738101-1

1 FRONT & REAR INSULATORS: HIGH-TEMP THERMOPLASTIC OR THERMOSET EPOXY PER ASTM D5948.
 CONTACT RETENTION CLIPS: STAINLESS STEEL PER AISI 302 OR COPPER ALLOY PER ASTM B194
 REAR GROMMET & INTERFACIAL SEAL: FLUOROSILICONE ELASTOMER PER MIL-R-25988 B EXCEPT 4.6.6.1.

2 PART TO BE MARKED WITH TE IDENTIFICATION, TE PART NO. AND DATE CODE: YEAR & WEEK (YY WW) IN APPROXIMATE AREA SHOWN.

- 3. THIS INSERT CONTAINS: 6 CAVITIES FOR SIZE 12 PIN CONTACTS
- 4. THIS PRODUCT IS SOLD BY TYCO ELECTRONICS UNDER A LICENSE FROM RADIALL SA.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C. THOMAS 10-8-09	TE Connectivity	
DIMENSIONS: mm		CHK K. HOGAN 10-9-09		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K. HOGAN 10-9-09	NAME INSERT ASSEMBLY, PIN, ARRANGEMENT 06, KEY B, GPRB	
0 PLC ± 1 PLC ± 2 PLC ±0.05 3 PLC ± 4 PLC ± ANGLES ± FINISH		PRODUCT SPEC -	SIZE A200779	
MATERIAL 1		APPLICATION SPEC -	DRAWING NO. C-1738101	RESTRICTED TO -
		WEIGHT -	SCALE 4:1	SHEET 1 OF 1
		CUSTOMER DRAWING	REV B	