


P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	REVISED (REDRAW)	16APR2013	T.N	N.Y
	G	REVISED PER ECR-17-004338	18APR17	C.L	N.Y
	GI	REVISED PER ECN-24-298077	24APR2025	RK	FJS



7-3	7-2	7-1	3	2	1	3	2	1	3	2	1
PART NO.											
1	-	-	-	-	-	1.8	7.2	BRASS,Ni PLATED	JACK-SCREW BODY	③	
-	1	-	-	-	-	2.6	26.0	BRASS,Ni PLATED	JACK-SCREW BODY	③	
-	-	1	-	-	-	3.65	7.2	BRASS,Ni PLATED	JACK-SCREW BODY	③	
-	-	-	1	-	-	1.8	7.2	BRASS,TIN PLATED	JACK-SCREW BODY	③	
-	-	-	-	1	-	2.6	26.0	BRASS,TIN PLATED	JACK-SCREW BODY	③	
-	-	-	-	-	1	3.65	7.2	BRASS,TIN PLATED	JACK-SCREW BODY	③	
1	1	1	1	1	1	-	-	STAINLESS STELL ORGANIC COATING	JACK-SCREW PIN	②	
1	1	1	1	1	1	-	-	STAINLESS STELL ORGANIC COATING	JACK-SCREW TIP	①	
QTY						"A"	"B"	MATERIAL&FINISH	NAME	ITEM	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL -

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±°

1 PLC ±°

2 PLC ±° ±0.4

3 PLC ±°

4 PLC ±°

ANGLES ±1°

FINISH -

DWN T.NAGASAKI 16APR2013

CHK S.YAMADA 16APR2013

APVD N.YAMASAKI 16APR2013

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

Customer Drawing

TE Connectivity

JACK-SCREW MALE
EXTRA-LONG
M SERIES

SIZE A300779

CAGE CODE C-170994

DRAWING NO

RESTRICTED TO -

SCALE 2:1

SHEET 1 OF 1

REV GI

1470-19 (3/11)