





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DF	00		0	CONVERTED RADIALL DWG TO TYCO ACAD DWG	11/03	—	—
			1	REVISED	22APR10	RF	JM

- 1
- FRONT & REAR INSULATORS: THERMOSET EPOXY PER ASTM D5948  
CONTACT RETENTION CLIPS: COPPER ALLOY PER ASTM B194  
REAR GROMMET: FLUOROSILICONE ELASTOMER PER MIL-R-25988 B, EXCEPT 4.6.6.1

- 2
- DATE CODE: YEAR & WEEK (YY WW)
3. DESCRIPTIVE PART NUMBER: GPRBE34SA  
THIS INSERT CONTAINS:  
16 CAVITIES FOR SIZE 20 SOCKET CONTACTS  
18 CAVITIES FOR SIZE 22 SOCKET CONTACTS
4. THIS PRODUCT IS SOLD BY TYCO ELECTRONICS  
UNDER A LICENSE FROM RADIALL SA.






MATING FACE



THIS PRINT IS  
**PRELIMINARY**  
UNQUALIFIED PRODUCT  
CONTACT PRODUCT ENGINEERING  
BEFORE USING THIS PRINT

1738179-1  
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R FLAIG		NOV03		<div> Tyco Electronics Corporation Harrisburg, PA 17105-3608</div>			
		CHK J MOSIER		NOV03					
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD J MOSIER		NOV03		NAME	
		0 PLC ± -		PRODUCT SPEC		GPR -B SOCKET INSERT CLASS E CONTACT ARRANGEMENT 34 KEY A			
		1 PLC ± -		—					
		2 PLC ± 0.05 [.002]		—					
		3 PLC ± -		APPLICATION SPEC					
		4 PLC ± -		—		SIZE		CAGE CODE	
MATERIAL		FINISH		WEIGHT		DRAWING NO		RESTRICTED TO	
- 		-		-		A2 00779		C=1738179	
CUSTOMER DRAWING						SCALE		SHEET	
						1:1		1 of 1	
								REV	
								1	