




4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

DIST

HB

—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—

PACKAGE SPEC	TE PART NO	PART A	PART B	DESCRIPTION	TYPE
107-79010	1-1721260-6	OJ-SH-112LMH2	12V	OJ-SH-112LMH2	q
	1-1721260-5	OJ-SH-112LMH2	12V	OJ-SH-112LMH2	p
107-84030	1-1721260-4	OJ-SS-105LMH2	5V	OJ-SS-105LMH2	0
	1-1721260-3	OJ-SS-112LMH2	12V	OJ-SS-112LMH2	n
	1-1721261-3	OJ-SH-112LMH2	12V	OJ-SH-112LMH2	m
107-79010	1-1721260-2	OJ-SH-124LMH2	24V	OJ-SH-124LMH2	l
	1-1721260-1	OJ-SH-112LMH2	12V	OJ-SH-112LMH2	k
	1-1721260-0	OJ-SH-109LMH2	9V	OJ-SH-109LMH2	j
	1721260-9	OJ-SH-106LMH2	6V	OJ-SH-106LMH2	i
	1721260-8	OJ-SH-105LMH2	5V	OJ-SH-105LMH2	h
	1721260-7	OJ-SH-103LMH2	3V	OJ-SH-103LMH2	g
	1721260-6	OJ-SS-124LMH2	24V	OJ-SS-124LMH2	f
	1721260-5	OJ-SS-112LMH2	12V	OJ-SS-112LMH2	e
	1721260-4	OJ-SS-109LMH2	9V	OJ-SS-109LMH2	d
	1721260-3	OJ-SS-106LMH2	6V	OJ-SS-106LMH2	c
	1721260-2	OJ-SS-105LMH2	5V	OJ-SS-105LMH2	b
	1721260-1	OJ-SS-103LMH2	3V	OJ-SS-103LMH2	a

RELAY TYPE

NOTES:

1.TERMINAL DIMENSION BEFORE TINNING.

2.LOT NO. SYSTEM AS FOLLOWING:

1

1

A

1

1

III

WEEK

YEAR

2.TERMINAL DIMENSION IS BEFORE SOLDER DIP;

3.FOR THE TIN-PLATING OF THE PINS:

+0.1mm FOR WIDTH,THICKENSS AND DIAMETER.

+0.5mm FOR LENGTH.

4.MARKING FROM INK TO LASER AND USING WELDED CONTACT

5.ADD LOT NO. SYSTEM AS FOLLOWING;

I, DIGITS FOR DAY OF THE WEEK

1...MONDAY IN THIS WEEK;

2...TUESDAY IN THIS WEEK;

7...SUNDAY IN THIS WEEK

II, DIGITS FOR SHIFT OF THE DAY

1...DAY SHIFT IN THIS DAY;

2...NIGHT SHIFT IN THIS DAY;

III, ONE CHARACTER DISTINGUISH THE LINE IDENTITY, SUCH AS: A,B,....Z

		EPOXY RESIN	SEAL (BASE & BOBBIN)	15
		3UEW	MAGNETIC WIRE	14
UL94V-0		P.B.T	CASE	13
UL94V-0		P.B.T	BASE	12
UL94V-0		P.B.T	BOBBIN	11
	SOLDER DIP	C.P WIRE	COIL TERMINAL	10
UL94V-0		P.P.S	CARD	9
		AgSn0In0	MOVABLE CONTACT	8
		AgSn0In0	NO.CONTACT	7
		STEEL	HINGE SPRING	6
	SOLDER DIP	Cu ALLOY	NO.TERMINAL	5
	SOLDER DIP	Cu ALLOY	MOVABLE SPRING	4
	NIP	STEEL	CORE	3
	NIP	STEEL	ARMATURE	2
	NIP	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

MATERIAL

FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

Hu,XieLi

Mak,Simon

Mingjung,Ho

—

—

—

CUSTOMER DRAWING

TE Connectivity

NAME

OJ-LMH2 SPEC

CUSTOMER DRAWING

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=

1721260

—

SCALE

SHEET

OF

REV

5:1

2

2

E2

1470-19

(3/11)