







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	REVISED PER ECN-25-313805	27MAR2025	TR	NSK





- NOTES :
- MATERIAL:
HOUSING: THERMOPLASTIC, UL 94V-0, COLOR: SEE TABLE.
CONTACT: PHOSPHOR BRONZE, THICKNESS=0.25mm.
SHELL: STAINLESS STEEL, THICKNESS=0.30mm.
 - FINISH:
CONTACT: GOLD FLASH OVER 0.762µm [30u"] MIN. PALLADIUM-NICKEL OR ALTERNATIVE 0.762µm [30u"] MIN. GOLD PLATING ON CONTACT AREA,
2.54µm [100u"] MIN. MATTE-TIN PLATING ON SOLDER TAILS,
1.27µm [50u"] MIN. NICKEL UNDERPLATED OVER ALL.
ⓔ SHELL: 2.54µm [100u"] MIN. NICKEL PLATED OVER
 - REFLOW SOLDER CAPABLE TO 260°C PER TE SPEC 109-201, CONDITION B.
- ⚠ PRELIMINARY PART.
- ⚠ CUSTOMER RESTRICTED PART, NOT FOR GENERAL SALES.




5	BLACK	1734517-5
4	BLUE	1734517-4
	WHITE	1734517-3
	BLACK	1734517-1
	H/S COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	20MAR2019	TE Connectivity Ltd.		
		CHK	21MAR2019			
		S.L.I	21MAR2019	NAME		
		APVD	21MAR2019			
		S.L.I		PRODUCT SPEC		
				APPLICATION SPEC		
				SIZE		
				CAGE CODE		
				DRAWING NO		
				RESTRICTED TO		
				SCALE		
				SHEET		
				REV		


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



- NOTES :
- MATERIAL:
HOUSING: THERMOPLASTIC, UL 94V-0, COLOR: BLACK.
CONTACT: PHOSPHOR BRONZE, THICKNESS=0.25mm.
SHELL: STAINLESS STEEL, THICKNESS=0.30mm.
MYLAR: POLYIMIDE FILM ADHESIVE TAPE, T=0.35MM
(HIGH TEMPERATURE-RESISTANT RANGE: 255°C TO 260°C, 5-10S)
 - FINISH:
CONTACT: GOLD FLASH OVER
0.762µm [30u"] MIN. PALLADIUM-NICKEL OR ALTERNATIVE 0.762µm [30u"] MIN. GOLD PLATING ON CONTACT AREA,
2.54µm [100u"] MIN. MATTE-TIN PLATING ON SOLDER TAILS,
1.27µm [50u"] MIN. NICKEL UNDERPLATED OVER ALL.
E SHELL: 2.54µm [100u"] MIN. NICKEL PLATED OVER
 - REFLOW SOLDER CAPABLE TO 260°C PER TE SPEC 109-201, CONDITION B.



SHOWN AS: 1734517-2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN —	20MAR2019	 TE Connectivity Ltd.				
		CHK S.LI	21MAR2019					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S.LI	21MAR2019	NAME USB B TYPE, TOP ENTRY, 4 POSITION, SMT TYPE		
		0 PLC ± 0.38 1 PLC ± 0.25 2 PLC ± 0.13 3 PLC ± 0.05 4 PLC ± — ANGLES ± 3°		PRODUCT SPEC 108-57538				
				APPLICATION SPEC —				
				WEIGHT —				
MATERIAL —		FINISH —		SIZE A3	CAGE CODE 00779	DRAWING NO C-1734517	RESTRICTED TO —	
CUSTOMER DRAWING						SCALE N/A	SHEET 2 of 3	REV E

