

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECN-25-314963	01APR2025	TR	RK

1. MATERIAL:

- 1.1 HOUSING: PA46, WITH 30% GF, UL94 V-0, BLACK COLOR.

- ### 1.2 CONTACTS: PHOSPHOR BRONZE.

- 1.3 SHELL: BRASS.

2. FINISH:









- ## 2.1 CONT

- 1.27um [50u"] MIN. NICKEL UNDERPLATED OVERALL.

- 2.2 SHELL: 0.508um [20u"] MIN. NICKEL PLATED.


- PCB GROUND: TIN PLATED.

- ### 3. REFLOW SOLDER CAPABLE





RECOMMENDED PCB LAYOUT  
RECOMMENDED PCB THICKNESS: 1.6mm.  
TOLERANCE:  $\pm 0.05$  (TOP VIEW)


OBSOLETE	TRAY	1.27um[50u"]	1-1734714-4
OBSOLETE		0.76um[30u"]	1-1734714-3
OBSOLETE		0.38um[15u"]	1-1734714-2
OBSOLETE		0.15um[6u"]	1-1734714-1
OBSOLETE		1.27um[50u"]	1734714-4
OBSOLETE	TUBE	0.76um[30u"]	1734714-3
		0.38um[15u"]	1734714-2
OBSOLETE		0.15um[6u"]	1734714-1
	PACKAGE	MIN.GOLD THICKNESS	PART NUMBER



SPLIT-PEGS



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CHIEN	20FEB2008		<div>TE Connectivity</div>			
		CHK S. HOU	20FEB2008					
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD W. KODAMA	20FEB2008		NAME			
	0 PLC ± — 1 PLC ± 0.3 2 PLC ± 0.2 3 PLC ± 0.15 4 PLC ± — ANGLES ± 3°	PRODUCT SPEC —	MODULAR JACK, RJ45, MULTI-PORT SHIELDED, THRU-HOLE, PANEL GROUND —					
		APPLICATION SPEC —						
MATERIAL —	FINISH —	WEIGHT 22.41 GRAMS	SIZE A3	CAGE CODE 00779	DRAWING NO C-1734714	RESTRICTED TO —		
CUSTOMER DRAWING					SCALE 1:1	SHEET 1 OF 2	REV B	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



- NOTES:
- 1. MATERIAL:
    - TUBE: PVC.
    - BOX: CORRUGATED FIBER.
  - 2. DIMENSION: SEE DRAWING
  - 3. QUANTITY: SEE TABLE
  - 4. WEIGHT: SEE TABLE

13.40KG	10.08G	9	50	450
GROSS WEIGHT	NET WEIGHT	PCS/ TUBE	TUBES/ BOX	PCS/ BOX

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CHIEN	20FEB2008	 TE Connectivity			
		CHK S. HOU	20FEB2008				
DIMENSIONS: mm		APVD W. KODAMA	20FEB2008	NAME MODULAR JACK, RJ45, MULTI-PORT SHIELDED, THRU-HOLE, PANEL GROUND —			
		PRODUCT SPEC —		SIZE CAGE CODE DRAWING NO			RESTRICTED TO —
		APPLICATION SPEC —					
MATERIAL —		FINISH —		WEIGHT 22.41 GRAMS			A300779C-1734714
				CUSTOMER DRAWING			
					SCALE 1:1	SHEET 2 of 2	REV B