




LOC	DIST	REVISIONS				
CM	00	P	LTR	DESCRIPTION	DATE	APVD
			A	RELEASED PER WR-07-024	28FEB07	DB



④ MATERIAL: CONNECTOR-NYLON UL94V-0 (BLACK).
CONTACTS-0.30 [.012] THICK COPPER ALLOY
GOLD PLATE 0.00076 [.000030] MIN THICK IN
CONTACT AREA WITH MATTE WHISKER MITIGATED
TIN OVER NICKEL UNDERPLATE IN WIRE SLOT
AREA.

2. CONTACTS ACCEPT 24 AWG WIRE WITH 1.52 [.060] MAX
INSULATION DIAMETER.

3. CONTACTS MUST ACCEPT 0.64±0.03 [.025±.001] SQUARE
POST AND REMAIN LOCKED IN POSITION.

④ IDENTIFICATION NUMBER FOR LAST CIRCUIT MAY
NOT APPEAR ON ALL ASSEMBLIES.

5. DIMENSIONS IN BRACKETS ARE IN INCHES.

6. HOUSING FEATURES ARE: FEED THRU WITH LOCKING
RAMP.



10.16 [.400]	4	3-1744273-4
DIM A	NO.OF POSN	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER	28FEB2007	tyco Electronics		Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm [INCHES]		CHK D. BOSSI	28FEB2007			NAME	
		APVD D. BOSSI	28FEB2007	PRODUCT SPEC		MTA .100 CONNECTOR ASSEMBLY 24 AWG, UL94V-0, SPECIAL	
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		108-1050		SIZE	
		0 PLC ±		APPLICATION SPEC		CAGE CODE	
		1 PLC ± 0.13 [.005]		114-1019		DRAWING NO	
MATERIAL		4 PLC ±		WEIGHT		RESTRICTED TO	
FINISH		±		CUSTOMER DRAWING		SCALE	
④		④		A2 00779		SHEET 1 OF 1	
						REV A	