





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20  
 © COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
1		DRAWN IN PRO-E	26FEB2009	DCB	JM		
2		REVISED	27APR2010	RF	JM		



MATING FACE



THIS PRINT IS  
**PRELIMINARY**  
 UNQUALIFIED PRODUCT  
 CONTACT PRODUCT ENGINEERING  
 BEFORE USING THIS PRINT

- 1 FRONT & REAR INSULATORS: HIGH-TEMP THERMOPLASTIC OR THERMOSET EPOXY PER ASTM D5948.  
CONTACT RETENTION CLIPS: STAINLESS STEEL PER AISI 302 OR COPPER ALLOY PER ASTM B194
- 2 PRODUCT IDENTIFICATION MARKINGS: TYCO ELECTRONICS LOGO  
PART NUMBER  
DATE CODE - YEAR & WEEK (YY WW)

- 3. DESCRIPTIVE PART NUMBER: GPRBN28PB  
THIS INSERT CONTAINS: 22 CAVITIES FOR SIZE 22 PIN CONTACTS  
6 CAVITIES FOR SIZE 16 PIN CONTACTS
- 4. THIS PRODUCT IS SOLD BY TYCO ELECTRONICS UNDER A LICENSE FROM RADIALL SA.

1738163-1  
 PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN DCB	26FEB2009	Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		CHK JM	APVD JM	NAME INSERT SUB-ASSEMBLY, PIN, ARRANGEMENT 28, NON-ENVIRONMENTAL, KEY B, GPRB	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±0.013 4 PLC ±0.0001 ANGLES ±- FINISH		PRODUCT SPEC -	APPLICATION SPEC -	SIZE A200779	CAGE CODE C-1738163
MATERIAL		WEIGHT -	CUSTOMER DRAWING	RESTRICTED TO -	SCALE 5:1 SHEET 1 OF 1 REV 2