



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		C	ADD -2 PER ECO 15-010716	7-22-15	CT	MS



- 1
- CONTACTS SUPPLIED AND PACKAGED SEPARATELY.
2.
- KEYING INSTALLED IN POSITION PER TABLE.
3.
- DUST COVER INSTALLED, NOT SHOWN FOR CLARITY.



SEE SHEET #2	"01"	NIC66SPNA150A01A	1757810-2
SEE SHEET #1	"01"	NIC66SPA120T2A01A	1757810-1
REMARKS	KEYING POSITION	DESCRIPTIVE NUMBER	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 4-25-05	TE Connectivity			
DIMENSIONS: INCHES [mm]		CHK K.HOGAN 4-26-05				
		APVD K.HOGAN 4-26-05	NAME SINGLE MOD,PLUG CONNECTOR ASSEMBLY, ARINC 600			
		PRODUCT SPEC				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE A2			
0 PLC ± -		—	CAGE CODE 00779			
1 PLC ± -		—	DRAWING NO C=1757810			
2 PLC ± -		—	RESTRICTED TO —			
3 PLC ± .010 [0.25]		—				
4 PLC ± -		—	SCALE 2:1			
ANGLES ± -		—				
FINISH		WEIGHT —	SHEET 1 of 2			
SEE CALLOUTS		CUSTOMER DRAWING				
SEE CALLOUTS		—	REV C			

Ø.151
Ø.230 X 82° CSK
4 PLC

150 POSN INSERT (-2)
REAR RELEASE/REMOVE
MATL: THERMOPLASTIC EPOXY
COLOR: BLACK

TE PART NO
& DATE CODE

RETAINING PLATE
MATL: ALUMINUM PER
QQ-A-250 OR QQ-A-591
FINISH: ELECTROLESS NICKEL PER AMS-C-26074

SHELL
MATL: ALUMINUM ALLOY PER
QQ-A-250 OR QQ-A-591
FINISH: ELECTROLESS NICKEL
PER AMS-C-26074

SAME AS -1 EXCEPT AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES [mm]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	.010 [0.25]
4 PLC	±	-
ANGLES	±	-
FINISH		SEE CALLOUTS

MATERIAL

SEE CALLOUTS

DWN: C.C.THOMAS 4-25-05

CHK: K.HOGAN 4-26-05

APVD: K.HOGAN 4-26-05

PRODUCT SPEC

APPLICATION SPEC

WEIGHT: -

CUSTOMER DRAWING

TE Connectivity

NAME: SINGLE MOD,PLUG CONNECTOR ASSEMBLY, ARINC 600

SIZE: A2

CAGE CODE: 00779

DRAWING NO: 1757810

RESTRICTED TO: -

SCALE: 2:1

SHEET: 2 OF 2

REV: C