


LOC		DIST		REVISIONS						
AF		50		P	LTR	DESCRIPTION		DATE	DWN	APVD
					A	DRAWN	29APR13	JR	TM	



SECTION C-C


- 1

FINISH: 0.8μM PRE-TIN OVER 0.5μM MIN COPPER.
- 2


WIRE RANGE: 20-16 AWG
- 3

CONTACTS COATED WITH TE ANTI-FRETTING LUBRICANT.
- 4





WIRE INSULATION RANGE: .067-.114 [1.7-2.9] DIA.



SECTION A-A
SCALE 20:1



SECTION B-B
SCALE 20:1



1744201-1		31	PHOS BRONZE	1744396-1			
STRIP NO.		FINISH	MATERIAL	PART NO.			
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 29APR13 CHK TOM MICHELUTTI 29APR13	STE TE Connectivity				
DIMENSIONS: INCHES [mm]		APVD TOM MICHELUTTI 29APR13					
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CONTACT, LANCELESS, STD. ECONOMY POWER II, LOOSE PIECE —				
	0 PLC ± —					PRODUCT SPEC	
	1 PLC ± —					—	
	2 PLC ± 0.2					APPLICATION SPEC	
	3 PLC ± 0.25					—	
	4 PLC ± —		SIZE CAGE CODE DRAWING NO			RESTRICTED TO	
	4. ANGLES						
	5. ANGLES						
MATERIAL	FINISH	WEIGHT	A100779C1744396			—	
CUSTOMER DRAWING			SCALE 10:1		SHEET 1 OF 1		REV A