

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	1-1776892-7 AND 2-1776892-2 OBSOLESCENCE	22MAY2024	SN	PS



1. MATERIAL:
HOUSING: POLYAMIDE 6 UL94V-2.
COLOR: NATURAL (OFF WHITE).
TUBULAR CONTACT: BRASS, TIN PLATED.
SCREW: M5, STEEL, ZINC PLATED W/ NON-HEXAVALENT CHROMATE (CHROME III).

2. ELECTRICAL:
CURRENT RATING: 65A, 600V.
WIRE RANGE: 6-14 AWG.

3. CONTINUOUS WORKING TEMP.: 100°C MAX.

- 4 CUTTING PROJECTION CAN BE ON BOTH SIDES
DEPENDING ON CUTTING LOCATION.

5. CUTTING BURR MAX. 1mm ALLOWED.



OBSOLETE	PHILLIPS HEAD	145.0	170.7	12	TSB200012K/12PM	2-1776892-2
OBSOLETE	PHILLIPS HEAD	72.5	98.2	7	TSB20007K/7PM	1-1776892-7
OBSOLETE	PHILLIPS HEAD	43.5	69.2	5	TSB20005K/5PM	1-1776892-5
OBSOLETE	SLOTTED HEAD	145.0	170.7	12	TSB200012K/12	1-1776892-2
	SLOTTED HEAD	72.5	98.2	7	TSB20007K/7	1776892-7
OBSOLETE	SLOTTED HEAD	43.5	69.2	5	TSB20005K/5	1776892-5
	SCREW TYPE	DIM B	DIM A	NO OF POS	T & B PART NUMBER	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 9/25/06	TE Connectivity Ltd.			
DIMENSIONS: mm		CHK C RICHARD 9/25/06				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C RICHARD 9/25/06	NAME 14.5MM PITCH, 65A HIGH VOLTAGE VERSION			
		PRODUCT SPEC	—			
0 PLC ± — 1 PLC ± 0.3 2 PLC ± 0.25 3 PLC ± — 4 PLC ± — ANGLES ± 2°		APPLICATION SPEC	—			
MATERIAL SEE NOTES		FINISH SEE NOTES	SIZE A3	CAGE CODE 00779	DRAWING NO C-1776892	RESTRICTED TO —
CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1	REV B2	