

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT 2004 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
JDIST
/


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
0		RELEASED (FJB0-1460-04)	24DEC04	E.L	W.K



1	INSULATION SHEET(SHUTTER BRACKET SURFACE)	⑨
1	INSULATION SHEET	⑧
2	NUT(M2x0.4)	⑦
1	BRACKET (R)	⑥
1	BRACKET (L)	⑤
1	LOWER SHELL	④
1	UPPER SHELL	③
1	PUSH-PUSH SUB ASSY	②
1	HEADER ASSY (BOTTOM TYPE , RIGHT BUTTON)	①
QTY	NAME	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± 0.5
1 PLC	± 0.5
2 PLC	± 0.5
3 PLC	± 0.5
4 PLC	± 0.5
ANGLES	±
FINISH	

DWN
E.LIU

24DEC04

CHK

T.FUTATSUGI

24DEC04

APVD

W.KODAMA

24DEC04

PRODUCT SPEC

108-78210

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

tyco
Electronics

 Tyco Electronics AMP K.K.
 Kawasaki, Japan

NAME

 CARDBUS CONNECTOR
 LOWER SLOT BOTTOM MOUNT TYPE
 PUSH-PUSH RIGHT BUTTON

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-1747836

SCALE 1:1

SHEET 1 OF 5

REV 0

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 2004 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
JDIST
/

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—








TABLE 1

POST LENGTH	5	3.5	4.25
CIRCUIT NO.	1, 17, 34, 35, 51, 68	36, 67	OTHERS

DETAIL A
SCALE 4:1±0.3
1.55
(STAND OFF)±0.3
1.65
(STAND OFF)±0.3
1.85
(STAND OFF)±0.3
9.5+0.1
0
0.2
(INSULATION SHEET)(0.15)
(GAP: INS./PCB)±0.3
0.35
(BRACKET)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± 0.5
1 PLC	± 0.5
2 PLC	± 0.5
3 PLC	± 0.5
4 PLC	± 0.5
ANGLES	±
FINISH	±

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

tyco
ElectronicsTyco Electronics AMP K.K.
Kawasaki, Japan

NAME

CARDBUS CONNECTOR
LOWER SLOT BOTTOM MOUNT TYPE
PUSH-PUSH RIGHT BUTTON

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-1747836

SCALE 1:1

SHEET 2 OF 5

REV 0

4

3

2

1


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



© COPYRIGHT 2004 BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
J			—	SEE SHEET 1	—	—



INSULATION SHEET AREA
(SCALE 2:1)



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± 0.5
1 PLC	± 0.5
2 PLC	± 0.5
3 PLC	± 0.5
4 PLC	± 0.5
ANGLES	±

FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

tyco
ElectronicsTyco Electronics AMP K.K.
Kawasaki, Japan

NAME

CARDBUS CONNECTOR
LOWER SLOT BOTTOM MOUNT TYPE
PUSH-PUSH RIGHT BUTTON

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-1747836

SCALE 1:1

SHEET 3 OF 5



REV 0

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 2004 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
J		SEE SHEET 1	—	—	—



NOTE

- 1 RECOMMENDED TIGHTENING TORQUE
:FROM 0.15N·m (1.5kg·cm) TO 0.2N·m(2kg·cm)
- 2 STAND OFF 1.85±0.3 AREA.
- 3 STAND OFF 1.65±0.3 AREA.
- 4 STAND OFF 1.55±0.3 AREA.
- 5 REFER TO TABLE 1 FOR POST CONTACT LENGTH.
- 6 KEEP OPEN CONDITION.
- 7 NO ELECTRONICS COMPONENTS.(NO SIGNAL LINE AREA)
- 8 GROUNDING PAD.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		Tyco Electronics AMP K.K.	
		CHK		Kawasaki, Japan	
		APVD		NAME	
		PRODUCT SPEC		CARDBUS CONNECTOR	
		APPLICATION SPEC		LOWER SLOT BOTTOM MOUNT TYPE	
		WEIGHT		PUSH-PUSH RIGHT BUTTON	
MATERIAL		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		A3	00779	C-1747836	—
CUSTOMER DRAWING		SCALE	1:1	SHEET	4 OF 5
		REV	0		

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT 2004 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
J

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



DETAIL A

0.6mm PITCH CARD EDGE CONNECTOR
FOR THIS CARDBUS PRODUCTS

Parts Number	Description
6123215-1	HARD TRAY ASSY
6376045-1	ON TAPING(EMBOSS)


COMMON		UPPER SLOT		LOWER SLOT	
PIN NO.	RECEIVER	PIN NO.	RECEIVER	PIN NO.	RECEIVER
B68	150	B34	75	B11	99
B34	149	B74	74	B45	98
B67	148	B73	73	B10	97
B33	147	B72	72	B44	96
B66	146	B71	71	B9	95
B32	145	B70	70	B43	94
B65	144	B69	69	B8	93
B31	143	B68	68	B42	92
B64	142	B67	67	B7	91
B30	141	B66	66	B41	90
B63	140	B65	65	B6	89
B29	139	B64	64	B40	88
B62	138	B63	63	B5	87
B37	137	B62	62	B39	86
B28	136	B61	61	B4	85
B61	135	B60	60	B38	84
B35	134	B59	59	B3	83
B60	133	B58	58	B2	82
B27	132	B57	57	B1	81
B60	131	B56	56	B37	80
B59	130	B55	55	B36	79
B25	129	B54	54	B35	78
B58	128	B53	53	B34	77
B24	127	B52	52	B33	76
B26	126	B51	51	B32	75
B23	125	B50	50	B31	74
B24	124	B49	49	B30	73
B56	123	B48	48	B29	72
B22	122	B47	47	B28	71
B55	121	B46	46	B27	70
B21	120	B45	45	B26	69
B54	119	B44	44	B25	68
B20	118	B43	43	B24	67
B53	117	B42	42	B23	66
B19	116	B41	41	B22	65
B18	115	B40	40	B21	64
B17	114	B39	39	B20	63
B16	113	B38	38	B19	62
B15	112	B37	37	B18	61
B14	111	B36	36	B17	60
B13	110	B35	35	B16	59
B12	109	B34	34	B15	58
B11	108	B33	33	B14	57
B10	107	B32	32	B13	56
B9	106	B31	31	B12	55
B8	105	B30	30	B11	54
B7	104	B29	29	B10	53
B6	103	B28	28	B9	52
B5	102	B27	27	B8	51
B4	101	B26	26	B7	50
B3	100	B25	25	B6	49
B2	99	B24	24	B5	48
B1	98	B23	23	B4	47
B0	97	B22	22	B3	46
B0	96	B21	21	B2	45
B0	95	B20	20	B1	44
B0	94	B19	19	B0	43
B0	93	B18	18	B0	42
B0	92	B17	17	B0	41
B0	91	B16	16	B0	40
B0	90	B15	15	B0	39
B0	89	B14	14	B0	38
B0	88	B13	13	B0	37
B0	87	B12	12	B0	36
B0	86	B11	11	B0	35
B0	85	B10	10	B0	34
B0	84	B9	9	B0	33
B0	83	B8	8	B0	32
B0	82	B7	7	B0	31
B0	81	B6	6	B0	30
B0	80	B5	5	B0	29
B0	79	B4	4	B0	28
B0	78	B3	3	B0	27
B0	77	B2	2	B0	26
B0	76	B1	1	B0	25
B0	75	B0	0	B0	24

PIN ASSIGNMENT
FOR BOTTOM MOUNT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

MM



MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± 0.5
1 PLC ± 0.5
2 PLC ± 0.5
3 PLC ± 0.5
4 PLC ± 0.5
ANGLES ±
FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

tyco
Electronics
Tyco Electronics AMP K.K.
Kawasaki, Japan

NAME

CARDBUS CONNECTOR
LOWER SLOT BOTTOM MOUNT TYPE
PUSH-PUSH RIGHT BUTTON

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-1747836

SCALE 1:1

SHEET 5 OF 5

REV 0