





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECR-25-250800	03FEB2025	F.Z	R.B



推奨基板取付け穴寸法
PC 基板厚: 1.6 ± 0.1
(非累積公差)
(コネクタ搭載面)

RECOMEND PC BOARD HOLE PATTERN
PC BOARD THICKNESS: 1.6 ± 0.1
(NOT ACCUMULATE TOLERANCE)
(CONNECTOR MOUNT SIDE)

- 1. MATERIAL: HOUSING: GLASS FILED THERMO PLASTIC, POLYESTER
CONTACT: COPPER ALLOY
RETENTION LEG: COPPER ALLOY
- 2. FINISH (CONTACT AREA): 0.38 μm PdNi & Au
PLATING OVER NICKEL
- 3. FINISH (CONTACT AREA): 0.76 μm PdNi & Au
PLATING OVER NICKEL
- 4. FINISH (CONTACT AREA): 2.0 μm MIN TIN
PLATED OVER NICKEL
- 5. NOTE DELETED
- 6. FINISH (RETENTION LEG): TIN PLATED
(CONTACT TAIL) OVER NICKEL
- 7. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE
THEY DON'T SHOW DETAILS
- 8. THE DATE CODE SHOW PRODUCTION LOT BY NUMBER.
THE NUMBER MAKE UP THE NUMBER OF FOUR COLUMNS
OR FIVE COLUMNS. (INCLUDE THE ALPHABET)

6	4	1-178295-5
6	3	1-178295-3
6	2	1-178295-2
(FINISH)		製品番号 (PART NO.)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N. MATSULARA 14 JUN 91	TE Connectivity		
		CHK H.OBATA 14 JUN 91			
		APVD N. MATSULARA 14 JUN 91	NAME 5 POS SINGLE ROW HORIZONTAL HDR ASS'Y FOR DYNAMIC 3100		
		PRODUCT SPEC			
		APPLICATION SPEC			
		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-178295
		CUSTOMER DRAWING	SCALE 1:1	SHEET 1 OF 1	REV C