




NUMBER 178305



METRIC

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT


PRINT DIST

コネクタ外形
OUTLINE OF HEADER HOUSING

10- $\phi 1.1$
DIA 1.1 ± 0.1 10 PLACES

スルーホール 2- $\phi 3$
DIA 3 ± 0.1 2 PLACES



ラウンド 2- $\phi 4$ MIN
ROUND DIA 4 MIN 2 PLACES

推奨基板取付け寸寸法

PC 基板厚: 1.6 ± 0.1
(非累積公差)
(コネクタ搭載面)

RECOMEND PC BOARD HOLE PATTERN

PC BOARD THICKNESS: 1.6 ± 0.1
(NOT ACCUMULATE TOLERANCE)
(CONNECTOR MOUNT SIDE)

VIEW A
(SCALE: 1:1)

NOTES

- MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC, POLYESTER
CONTACT: COPPER ALLOY
RETENTION LEG: COPPER ALLOY
- FINISH (CONTACT AREA): 0.38 μ m PdNi & Au PLATING OVER NICKEL
- FINISH (CONTACT AREA): 0.76 μ m PdNi & Au PLATING OVER NICKEL
- FINISH (CONTACT AREA): 2.0 μ m MIN TIN PLATED OVER NICKEL
- FINISH (RETENTION LEG): TIN LEAD PLATED (CONTACT TAIL) OVER NICKEL
- FINISH (RETENTION LEG): TIN PLATED (CONTACT TAIL) OVER NICKEL

6	4	178305-5
5	3	178305-3
6	2	178305-2
(FINISH)		製品番号 (PART NO.)

D	REVISED PER ECR-25-250788	F.Z	R.B	16 JAN 2025
C2	REVISED PER ECO-11-005030	RK	HMR	25 APR 11
LTR	REVISION RECORD	DR	CHK	DATE

WIRE RANGE		INSULATION DIA	NAME ダイナミック D3100 水平タイプ 10 極 ヘッダーアセンブリ	
MATERIAL SEE NOTE 注記参照		FINISH SEE NOTE 注記参照	10 POS DOUBLE ROW HORIZONTAL HDR ASS'Y FOR DYNAMIC 3100	
DR. 14 JUN 91 N. Matsubara		DE. 14 JUN 91 N. Matsubara	一般公差 (GENERAL TOLERANCE)	SIZE LOC NUMBER
CHK. 24/FEB/92 H. Oota		APP. 4/MAR/92 S. MANABE	10mm $\pm$ 0.3 10mm $\pm$ 0.4 30mm $\pm$ 0.45 角 度: $\pm 3^\circ$	A3 J C-178305
			SCALE 2-1	REV. D SHEET 1 OF 1

(CUSTOMER DRAWING) 顧客用図面