





P	LTR	DESCRIPTION	DATE	DWN	APVD
	D2	REVISED PER ECO-11-005030	24MAR2011	RK	HMR
	E	REVISED PER ECR-20-003937	16MAR2020	T.S	E.I
	F	REVISED PER ECR-25-250757	15JUL2025	F.Z	R.B



RECOMEND PC BOARD HOLE PATTERN
PC BOARD THICKNESS:1.6±0.1
(NOT ACCUMULATE TOLERANCE)
(CONNECTOR MOUNT SIDE)

- 1. MATERIAL:HOUSING :GLASS FILED THERMO PLASTIC,POLYESTER
CONTACT: COPPER ALLOY
RETENTION LEG: COPPER ALLOY
- 2 FINISH(CONTACT AREA): 0.38µm PdNi & Au PLATING OVER NICKEL
- 3 FINISH(CONTACT AREA): 0.76µm PdNi & Au PLATING OVER NICKEL
- 4 FINISH(CONTACT AREA): 2.0umMIN TIN PLATED OVER NICKEL.
- 5. NOTE DELETED
- 6 FINISH(RETENTION LEG): TIN PLATED
(CONTACT TAIL) OVER NICKEL.
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.



2-178318-2,-3,-5
KEY TYPE Y

Y	6	4	2-178318-5	OBSOLETE 7
	6	3	2-178318-3	
	6	2	2-178318-2	
X	6	4	1-178318-5	
	6	3	1-178318-3	
	6	2	1-178318-2	
KEYING	FINISH	PART NO		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SHIMOYASU 16MAR2020	TE Connectivity		
		CHK E.IKEMATSU 16MAR2020			
		APVD E.IKEMATSU 16MAR2020	NAME 10POSN VERTICAL HEADER ASSEMBLY DYNAMIC D3100S		
DIMENSIONS: mm		PRODUCT SPEC 108-5349			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APPLICATION SPEC -	SIZE A3		
	0 PLC ±0.3 1 PLC ±0.3 2 PLC ±0.3 3 PLC ±0.3 4 PLC ±- ANGLES ±3	WEIGHT -			
MATERIAL -	FINISH -	CUSTOMER DRAWING	CAGE CODE 00779	DRAWING NO C-178318	RESTRICTED TO -
			SCALE 2:1	SHEET 1 OF 1	REV F