

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-



COPYRIGHT 2011

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD



C

REVISED AS PER ECN-22-176158





23JUL2022

HS

SZ



RECOMMEND P.C.B LAYOUT



NOTES:

1. MATERIAL:

HOUSING: THERMOPLASTIC, 30% G/F RATED,
UL 94V-0, COLOR: GRAY.

CONTACT: PHOSPHOR BRONZE, T=0.25mm.

SHELL: PHOSPHOR BRONZE, T=0.40mm.

2. FINISH :

CONTACT: GOLD FLASH OVER 30μ" MIN. PALLADIUM-NICKEL OR
ALTERNATIVE 30μ" MIN. GOLD PLATING ON CONTACT AREA.
100μ" MIN. MATTE TIN PLATING ON SOLDER TAILS
50μ" MIN. NICKEL UNDERPLATING OVERALL.


SHELL: 50μ" MIN. NICKEL PLATING OVERALL.

3. REFLOW SOLDER CAPABLE TO 260 PER TE SPEC. 109-201,
CONDITION B.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



MATERIAL

SEE NOTE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± 0.30
2 PLC ± 0.20
3 PLC ± -
4 PLC ± -
ANGLES ± 3°

FINISH

SEE NOTE

DWN 06JUN2006

O. HU

CHK 06JUN2006

S. HOU

APVD 06JUN2006

W.J. KE

PRODUCT SPEC

108-57062

APPLICATION SPEC

WEIGHT

0.55 GRAMS

CUSTOMER DRAWING



TE Connectivity

NAME

MINI USB CONN., RCPT, AB,
FLANGE TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C=1775378

SCALE

SHEET

1 OF 2

REV

C

1775378-1

PART NUMBER

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-



COPYRIGHT 2011

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1.

NOTES:

1. MATERIAL :

1.1 EMBOSSED CARRIER: PS

1.2 COVER TAPE: PS

1.3 SHIPPING CARTON: CORRUGATED FIBER

2. DIMENSION :

2.1 REEL: W=24.0

2.2 SHIPPING CARTON: L=348, W=348, H=340

3. QUANTITY :

3.1 PRIMARY PACKING: 800PCS/REEL

3.2 SECONDARY PACKING: 10

REELS/CARTON(8,000PCS)


4. WEIGHT :

4.2 NET WEIGHT: 1.05KG/REEL, 10.5KG/CARTON.


4.1 GROSS WEIGHT: 1.15KG/REEL, 11.5KG/CARTON.

5. PEELING RESISTANCE: 10.2gf~71.4gf.

6. PEELING SPEED: 300mm/minutes.



PULL OUT DIRECTION


(EMPTY)
END SECTION
(160mm MIN.)

(EMPTY)

LEADING SECTION

4000mm Min.


W/ PRODUCT CHARGE

PEELING DIRECTION
165°~180°
PEELING ANGLE

ø330

ø13

LABEL



11.50±0.10

1.75±0.10


2.00±0.10

4.00±0.10

16.00±0.10

ø1.50±0.10

24.00±0.30




4.92

7.43


5.31

7.0




348


348



340



SHIPPING CARTON




H

L

W

LABEL



7.43

5.97

4.75

3.20

0.99

4.20

4.50

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC


APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

FINISH

±

±

±

±

±

±

±

DWN	—
CHK	—
APVD	—
PRODUCT SPEC	—
APPLICATION SPEC	—
WEIGHT	—
CUSTOMER DRAWING	—



TE Connectivity

NAME

MINI USB CONN., RCPT, AB,
FLANGE TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C=1775378

SCALE

SHEET

2 OF 2

REV

C