




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		INITIAL RELEASE	26AUG2013	TV	IS
B		ADD HOLES AND MOVE MATERIAL MARKING	05JUN2014	TV	IS

CAVITY MARKING




MALE BOX LOCKING
 INTERFACE ACCORDING
 TO TE INTERFACE
 DRAWING 1801632



FEMALE BOX LOCKING
 INTERFACE ACCORDING
 TO TE INTERFACE
 DRAWING 1801632

△2 SPT 3 - 5 mm ²	0-0144433-1	/
△2 SPT 1 - 3 mm ²	0-0144617-1	/
△2 SPT 0.5 - 1 mm ²	0-0927831-2	/
△1 JPT 2.5 - 4 mm ²	0-1241978-2	/
△1 JPT 1 - 2.5 mm ²	0-0965999-2	/
△1 JPT 0.5 - 1 mm ²	0-0964284-2	/
△1 JPT 0.2 - 0.5 mm ²	0-0964280-2	/
ELECTRONIC DEVICE ISO 7588-2 TYPE C	/	MAX. DIMENSIONS : 30.6x30.7x55 TAB ACCORDING TO : ISO 8092
40A RESISTANCE RELAY ISO 7588-1 TYPE A	/	MAX. DIMENSIONS : 28x28x30 TAB ACCORDING TO : ISO 8092
DESCRIPTION	TE PN	COMMENTS
APPLIED COMPONENTS		



PP GFM 25/15	BLACK	1801618-1	E
MATERIAL	COLOR	TE PN	TE PRC PART REVISION

HOLDER LOADING CAPACITY	QUANTITY	1	1
	DESIGNATION	40A RELAY OR	ELECTRONIC DEVICE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN	I.VERNIER	19AUG2013	
		CHK	J.DREUX	19AUG2013	
MATERIAL	FINISH	APVD	J.SMIRANI	19AUG2013	
		PRODUCT SPEC	108-15412		
SEE TABLE		APPLICATION SPEC	408-15010		
		WEIGHT	21g		
		CUSTOMER DRAWING	SCALE	2:1	SHEET 1 OF 1

STE TE Connectivity

NAME: RELAY 40A HOLDER

RESTRICTED TO: -

SIZE: A2 CAGE CODE: 00779 DRAWING NO: C-1801618