




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A5	REVISED PER ECR-17-014951	16OCT2017	BDA	KR
	B	REVISED PER ECR-24-218682	09SEP2024	AK	BR
	B1	REVISED PER ECR-24-224610	10MAR2025	AK	BR




- MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOCK CAP OR HEADER
 - SMALL NICKS ARE PERMITTED ON THE CIRCUIT TOWERS WHICH COULD INCREASE THE INITIAL HOUSING MATING FORCE BY UPTO 4.4N [1.0 LBS]. NO INDIVIDUAL NICKED TOWER SHALL INCREASE THIS FORCE BY OVER 2.2N [.5LBS]
 - DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.
- 4 FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL
- 5 UNDERWRITERS RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE ON EACH SIDE OF HOUSING
- 6 NYLON, UL94V-2
- 7 MATERIAL CORRESPONDING TO THE REQUIREMENTS OF IEC 60335 (INCL. GLOW WIRE TEST 750°C WITHOUT FLAME)
- 8 PRELIMINARY PART NOT RELEASED FOR PRODUCTION




DETAIL A
SCALE 3:1
OPTIONAL CONSTRUCTION

OBSOLETE

7	NATURAL	PA66 UL94-V0 GWT 750°C	1-1863003-2	3
8	NATURAL	PA6 UL94-V0	1-1863003-1	2
7 6	NATURAL	PA6 UL94-V2	1863003-1	1
REMARK	COLOUR	MATERIAL	PART No	SL No



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SALO 29NOV2007	 TE Connectivity		
DIMENSIONS: INCH [mm]		CHK J. LAZARO 29NOV2007			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD L. BATILLO 29NOV2007			
0 PLC ± 1 PLC ± 2 PLC ±0.13 [.005] 3 PLC ± 4 PLC ± ANGLES ±0.5°		PRODUCT SPEC -			
MATERIAL SEE TABLE		APPLICATION SPEC -	NAME 9P UMNL PLUG HOUSING		
FINISH -		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-1863003
-		CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 1	REV B1