




1. MATERIALS & FINISH
HOUSING : HIGH TEMPERATURE POLYAMIDE,
UL 94V-0 RATED, COLOR: BLACK
CONTACT : COPPER ALLOY, TIN PLATED
2. MECHANICAL
MIN. PC BOARD HOLES DIAMETER : 1.4 mm.
MAX. PC BOARD THICKNESS : 2.4 mm.
3. ELECTRICAL
WIRE RANGE : 12 - 30 AWG
MAX. VOLTAGE : 300 V
MAX CURRENT : 15 A
CONTACT RESISTANCE : <15 m Ohm
INSULATION RESISTANCE : >1000 M Ohm (500V DC)
4. OPERATING TEMPERATURE RANGE: -40°C TO +105°C
5. TOLERANCE NOT CUMULATIVE.
6. RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC. FILE NO E60677.
7. TAPE AND REEL PACKAGING
8. OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON	06 JUN 2005		 TE Connectivity	
		CHK C. RICHARD	06 JUN 2005			
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD C. RICHARD	06 JUN 2005		NAME	
mm		PRODUCT SPEC			TERMINAL BLOCK HEADER ASSEMBLY 180 DEGREE, CLOSED ENDS, 5.00mm PITCH 5.00mm PITC	
	0 PLC ± 1 PLC ±0.5 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ±±	APPLICATION SPEC			SIZE	CAGE CODE
MATERIAL	FINISH	WEIGHT			DRAWING NO	
SEE NOTES	SEE NOTES	-	A2		00779	C-1776146
CUSTOMER DRAWING			SCALE		6:1	SHEET
					1	OF 2
					REV	A4



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET I	-	-	-



FOR TAPE AND REEL PARTS.





FIGURE A

FIGURE B

FIGURE C

6	56.0
4	44.0
3	32.0
NUMBER POS	DIM W

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
SEE NOTES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±0.5
2 PLC ±0.25
3 PLC ±-
4 PLC ±-
ANGLES ±-
FINISH

SEE NOTES

DWN S. WELDON 06JUN2005
CHK C. RICHARD 06JUN2005
APVD C. RICHARD 06JUN2005

PRODUCT SPEC
APPLICATION SPEC
WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME
TERMINAL BLOCK HEADER ASSEMBLY
180 DEGREE, CLOSED ENDS,
5.00mm PITCH 5.00mm PITC

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-1776146

RESTRICTED TO

SCALE 6:1
SHEET 2 OF 2
REV A4