







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A4		REVISED PER ECR-17-014951	16OCT2017	BDA	KR
B		REVISED PER ECR-24-218682	09SEP2024	AK	BR
B1		REVISED PER ECR-24-224610	10MAR2025	AK	BR

1. MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ CAP OR HEADER.
2. SMALL NICKS ARE PERMITTED ON THE CIRCUIT TOWERS WHICH COULD INCREASE THE INITIAL HOUSING MATING FORCE BY UP TO 4.4 NEWTONS [1.0 LBS]. NO INDIVIDUAL NICKED TOWER SHALL INCREASE THIS FORCE BY OVER 2.2 NEWTONS [1.5 LBS].
3. DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.
4. FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
5. NOT MANUFACTURED IN US.
6. UNDERWRITERS RECONGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE ON EACH SIDE OF HOUSING.
7. MATERIAL CORRESPONDING TO THE REQUIREMENTS OF IEC 60335 (INCL.GLOW WIRE TEST 750°C. WITHOUT FLAME)
8. PRELIMINARY PART NOT RELEASED FOR PRODUCTION.



OBSOLETE		NATURAL	PA66 UL94-V0 (GW T 750°C)	1-1863005-2
		NATURAL	PA6 UL94-V0	1-1863005-1
		NATURAL	PA6 UL94-V2	1863005-1
REMARKS		COLOUR	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: 19OCT2013 CHK: KARTHICK BALAJI APVD: KARTHICK BALAJI RAJENDRA PAI	NAME: UMNL 12 WAY PLUG HSG	
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	SIZE	CAGE CODE
mm	0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 3 PLC ± - 4 PLC ± -	108-1031	A1	-
	ANGLES ± "30"	APPLICATION SPEC	DRAWING NO	RESTRICTED TO
MATERIAL	FINISH	114-18011	SCALE 4:1	SHEET 1 OF 1
-	-	WEIGHT -	REV B1	
-	-	CUSTOMER DRAWING		