

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , - .

REVISIONS

© COPYRIGHT - TE Connectivity Ltd.

ALL RIGHTS RESERVED.

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	CUTTING BURR DETAILS ADDED	15NOV2018	RK	PS

1. MATERIAL:
 HOUSING: POLYAMIDE 6 UL94V-2.
 COLOR: NATURAL (OFF WHITE).
 TUBULAR CONTACT: BRASS TIN PLATED.
 SCREW: STEEL, ZINC PLATED W/ NON-HEXAVALENT CHROMATE (CHROME III).


2. CURRENT RATING: 40A.
 OPERATING VOLTAGE: 250V.
 WIRE RANGE: 10-24AWG.

3. CONTINUOUS WORKING TEMPERATURE 100°C.

4. CUTTING PROJECTION CAN BE ON BOTH SIDES DEPENDING ON CUTTING LOCATION.

5. CUTTING BURR MAX. 1mm ALLOWED.

12.0	31.5	3	TSB100003KDS	1776942-3
DIM B	DIM A	NO. OF POSN	T & B PART NUMBER	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 11/9/06	 TE Connectivity Ltd.	
DIMENSIONS: mm		CHK C RICHARD 11/9/06		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C RICHARD 11/9/06	NAME 12.0 PITCH, 40A EUROPA TERMINAL BLOCK	
0 PLC ± - 1 PLC ± 0.3 2 PLC ± 0.25 3 PLC ± - 4 PLC ± - ANGLES ± 2°		PRODUCT SPEC -	RESTRICTED TO -	
MATERIAL SEE NOTES		FINISH SEE NOTES	APPLICATION SPEC -	SIZE A3
		WEIGHT -	CAGE CODE 00779	DRAWING NO C=1776942
		CUSTOMER DRAWING	SCALE NTS	SHEET 1 OF 1
			REV A1	

1470-19 (1/15)