

NUMBER
178298



METRIC

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT DIST

AMP-J
REV.10/83

回路番号
CIRCUIT NO

AMPマーク
シリーズマーク
SERIES MARK

タブコンタクト
TAB CONTACT

リテンションレグ
RETENTION LEG

コンタクト半田付部
CONTACT TAIL

KEY TYPE X
1-178298-2,-3,-5

KEY TYPE Y
2-178298-2,-3,-5

Y	2-178298-5	△6	△4
	2-178298-3	△6	△3
	2-178298-2	△6	△2
X	1-178298-5	△6	△4
	1-178298-3	△6	△3
	1-178298-2	△6	△2
KEY TYPE	製品番号 (PART NO.)	(FINISH)	

C	REVISED PER ECR-25-250788	F.Z	R.B	16JAN 2025	
B	REVISED(FJD0-0039-03)	T.S	S.H	8/2 10/2	
A	REVISED(FJD0-0114-03)	T.S	S.M	25.APR '03	
O	RELEASED (FJ00-0017-93)	Y.T	S.M	2/8 '93	
LTR	REVISION RECORD	DR	CHK	DATE	

Copyright © 1993 AMP(Japan) LTD. ALL RIGHTS RESERVED.					
WIRE RANGE mm ² (AWG -)		INSULATION DIA mmφ		NAME 10 POS SINGLE ROW HORIZONTAL HDR ASS'Y FOR DYNAMIC 3100	
MATERIAL SEE NOTE 注記参照		FINISH SEE NOTE 注記参照		一般公差 (GENERAL TOLERANCE) 10mm以下 : ±0.3 10mm超 30mm以下 : ±0.4 30mm超 100mm以下 : ±0.5 角 度 : ±3°	
DR. 20-JAN-'93 Y.TANAKA		DE. 20-JAN-'93 Y.TANAKA		SIZE A3	LOC J
CHK. 8-FEB-'93 S.MANABE		APP. 8-FEB-'93 S.MANABE		SCALE 2-1	REV. C
				NUMBER C-178298	SHEET 1 OF 1

(CUSTOMER DRAWING) 顧客用図面