


DRILLED HOLE	:1,15	±0,025	mm
FIN. HOLE	:0,94	to 1,09	mm
AFTER REFLOW	:0,91	to 1,09	mm
Cu-thks	:0,025	to 0,075	mm
SnPb-thks	:0,004	to 0,010	mm



- 1 CONNECTOR MEETS THE REQUIREMENTS
ACC. DIN 41612 AND DIN 41611, PART 2 AND 5.
- 2 MATERIAL CONTACT: PHOSPHORBRONZE.
MATERIAL HOUSING: GLASSFILLED THERM. POLYESTER.
- 3 AT CONTACT AREA 0,8 μm GOLD OVER 1,25 μm NICKEL.
REMAINDER 1,25 μm TIN-LEAD (93/7).
- 4 CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE ON OUTSIDE
OF MATING AREA OF ROW c.
- 5 AT CONTACT AREA AND AREA 0,8 μm GOLD OVER 1,25 μm NICKEL.
AT ACTION PIN AREA 1,25 μm TIN LEAD (93/7).



P Q S	ROW abc		
	a	b	c
32	0	.	0
31	0	.	0
30	0	.	0
29	0	.	0
28	0	.	0
27	0	.	0
26	0	.	0
25	0	.	0
24	0	.	0
23	0	.	0
22	0	.	0
21	0	.	0
20	0	.	0
19	0	.	0
18	0	.	0
17	0	.	0
16	0	.	0
15	0	.	0
14	0	.	0
13	0	.	0
12	0	.	0
11	0	.	0
10	0	.	0
9	0	.	0
8	X	.	X
7	X	.	X
6	X	.	X
5	X	.	X
4	X	.	X
3	X	.	X
2	X	.	X
1	X	.	X

AN ASTERISK ,,X'' DENOTES A W.W. CONTACT.
AN ASTERISK ,,O'' DENOTES A B.T.B. CONTACT.

DIMENSIONS IN mm

METRIC

THIRD ANGLE
PROJECTION



5	2	OBS
3	2	1-188414-4
FINISH	MATERIAL	188414-4
		PARTNUMBER

---	---	-	-	-	CUSTOMER DRAWING		FOR REFERENCE ONLY WILL NOT BE UPDATED			
---	---	-	-	-	© COPYRIGHT 19--		BY AMP-HOLLAND B.V.			
---	---	-	-	-	ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING					
---	---	-	-	-	THIS DRAWING IS UNPUBLISHED					
					RELEASED FOR PUBLICATION		, 19--			
E1	EH-1209-00	RvH	R.F.	23 NOV 00			AMP-HOLLAND B.V. 's-Hertogenbosch, The Netherlands.			
A	EH-0826-94	LvdH	RvL	15 NOV '94			NAME		64 POS FEMALE CONN. ASS'Y ACC. DIN 41612 WITH ACTION-PIN FOR 1,6mm. P.C.BOARD THK'S	
O	EH-0687-94	LvdH	RvL	14 OCT '94						
LTR.	REVISION RECORD		DR.	CHK.	DATE					
DR.:	R.v.Lokven	CHK.:	R. FIJTEN	APP.:	B. FIJTEN	DWG.No.	C-188414	REV.LTR.	SHEET	
DATE:	19 July '94	DATE:	23 NOV 00	DATE:	23 NOV 00			E1	1 OF 1	
									A3	