


180416

AMERICAN PRODUCTION

TE PART No	MATERIALE (MATERIAL)	NOTE
<del>180416-1</del>	OTTONE (BRASS)	FORNITO AVVOLTO SU BOBINA IN CARTONE (REEL) ON STD. CARTON REEL
180416-2	OTTONE STAGNATO (BRASS TIN PLTD)	
<del>180416-3</del>	OTTONE (BRASS)	FORNITO AVVOLTO SU BOBINA IN CARTONE CON CARTA INTERPOSTA (REEL) ON STD. CARTON REEL WITH INTERLAYER PAPER STRIP
<del>180416-4</del>	OTTONE STAGNATO (BRASS TIN PLTD)	



SE NON DIVERSAMENTE INDICATO TOLLERANZA ±0,4

- 1 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 2 OBSOLETE

H2	ECR-10-022530	KK	HMR	11FEB11
H1	REVISED PER ECO-09-026346	KK	AEG	26NOV 09
H	Revised EToo-0067-01	G.S.	09/03/01	
D	AGGIUNTO P/N - 3 E - 4 TC		18-4-89	
C	CHANGED TOLERANCES DIM. 19 WAS 18,5	RR	5-11 68	
B	3,7 mm. WAS 2,8 mm. <i>DR</i>		1-19-67	
B	7,1 mm. WAS 8 mm. <i>DR</i>		1-19-67	
A	PART N. WAS 1A-5-5009	N.I.	3/4/65	
LTR	REVISION RECORD	DR	CHK	DATE
DR	N. ISKRA	DE		
CHK	2/25/65	APP		

© 1965 BY TE INCORPORATED ALL RIGHTS RESERVED. TE PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

CUSTOMER COPY REFERENCE ONLY

MATERIAL AND FINISH		
VEDI TABELLA (SEE TABLE)		
WIRE	RANGE	INSULATION
0,5-1,5 mm <sup>2</sup>		3 mm $\phi$
TOLERANCE EXCEPT AS NOTED	SCALE	LOC
±0,4	A-1	I
NAME		
SPADE TONGUE		

<b>TE</b> TE Connectivity	
CLASS	A.M.
TYPE	SQ. T.
NO	C-180416
REV	H2

DIMENSIONS IN MM DO NOT SCALE PRINT